

## EPIC® H-A 004 CL

H-A inserts with cage clamp termination up to 2.5 mm<sup>2</sup> wire cross section

The rectangular connector insert with cage clamp connection is perfect for anyone who wants to assemble without special tools. It ensures a vibration-proof connection and is made of a robust, non-flammable plastic in accordance with UL94 V-0. The 3+PE insert fits into EPIC® H-A 3 series housing and also has UL approval.



Supplementary automation components from Lapp



Mechanical and plant engineering



Rail



Wind Energy



Maximum vibration protection



Assembly time



Space requirement

### Benefits

Easy to assemble due to straight conductor entry

Cage clamp connection allows assembly without special tools and creates a vibration-proof connection between contact and cable. Strands can be connected with or without end sleeves.

Made of robust plastic (flammability class V-0 according to UL94 test method for the flammability of plastics).

Designed for use where space is limited thanks to small size.

UL certification according to technical data enables the use of the product in the North American region.

## EPIC® H-A 004 CL

### Application range

For power supply connection of devices and machines in various applications.

For use with EPIC® H-A 3 series housings

Suitable for outdoor use, taking into account the temperature range.

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000438 ETIM 5.0 Class-Description: Contact insert for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000438 ETIM 6.0 Class-Description: Contact insert for industrial connectors
Rated voltage (V):	IEC: 230 V / 400 V UL: 600 V
Rated impulse voltage:	4 kV
Rated current (A):	10 A
Flammability:	UL94 V-0
Contact resistance:	< 1 mOhm
Contacts:	Silver-plated brass
Number of contacts:	4 + PE
Termination methods:	Cage clamp termination: 0.14 - 2.5 mm <sup>2</sup> Cage clamp termination: 26 - 14 AWG
Material:	PC, polycarbonate
Cycle of mechanical operation:	500
Temperature range:	-40 °C to +125 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-A 004 CL**

Article number	Article description	Contact type	Wire protection	Packaging unit
44424057	EPIC H-A 004 M CL	male	yes	10
44424058	EPIC H-A 004 F CL	female	yes	10

Last Update (12.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16