
EPIC® SIGNAL M23 G6

Circular connectors for Servo Cables and encoders

EPIC® M23 panel base for bore hole, back wall assembly

Info
Made in Germany





- Mechanical and plant engineering
- Wind Energy
- Good chemical resistance
- Robust
- Interference signals

Benefits
Fast and easy assembly
Only one M25 bore hole necessary

Application range
Plant engineering
Servo drives and servo assemblies
Measurement and control technology

Technical Data
Classification ETIM 5: ETIM 5.0 Class-ID: EC000437

Last Update (28.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® SIGNAL M23 G6

	ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: nickel-plated zinc die-casting Sealing: FPM
Protection rating:	IP68 (10h/1m)
VDE-tested:	Certified production control: VDE-REG. no. C24 (according to EN 61984, SELV according to DIN VDE 0100-410 has to be guaranteed) UL File Number: E249137
Temperature range:	-25°C up to +125°C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

EPIC® SIGNAL M23 G6

Article number	Article	Coding	Fastening type	Pieces / PU
Type M23 G6 panel-mount box, rear wall mounting				
44420071	M23 G6	black (N)	M25 x 1.5 (with nut)	5
44420073	M23 G6	black (N)	M25 x 1.5 (with nut)	20

©2024 Lapp Group - Technical changes reserved