

MC 10.0 machined contacts

For inserts and modules of the EPIC® rectangular connectors

The modular crimping contacts 10.0 are suitable for maximum cross-sections and currents and their internal resistance is less than 1 milliohm.

Info

Crimping contacts for maximum cross sections and currents
silver plated and passivated contacts



Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Contact resistance:

< 1 mOhm

Material:

Copper alloy, hard silver-plated

Cycle of mechanical operation:

500

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

MC 10.0 machined contacts

Article number	Article description	Inserts	Version	Cross-section (mm ²)	Surface	Packaging unit
Contacts						
44424032	Modular SCEM AG 50 D=10.0	Crimping contacts for HHC1 modules	male	50	Ag	10
44424035	Modular BCEM AG 50 D=10.0	Crimping contacts for HHC1 modules	female	50	Ag	10
44424033	Modular SCEM AG 70 D=10.0	Crimping contacts for HHC1 modules	male	70	Ag	10
44424036	Modular BCEM AG 70 D=10.0	Crimping contacts for HHC1 modules	female	70	Ag	10
44424034	Modular SCEM AG 95 D=10.0	Crimping contacts for HHC1 modules	male	95	Ag	10
44424037	Modular BCEM AG 95 D=10.0	Crimping contacts for HHC1 modules	female	95	Ag	10
Crimping die for contacts of HHC1 modules						
44424038	TOOL DIE D=10.0/50 mm ²	Crimping dies	-	50	-	1
44424039	TOOL DIE D=10.0/70 mm ²	Crimping dies	-	70	-	1
44424040	TOOL DIE D=10.0/95 mm ²	Crimping dies	-	95	-	1

Last Update (12.07.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

MC 10.0 machined contacts