EPIC® H-B 10 TBFH-LB

Housing design H-B. The industry standard.


The metal housing with a single lever and a direct cable entry is suitable for use in lighting and sound systems.

Info

More interior space for wiring
Single Lever version for quick locking and simple unlocking with lifting aid
Protection rating UL50E tested







Supplementary automation components from Lapp

Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits

The smallest housing with single and double lever. The right housing is available for every application

Application range

Plant engineering
Light & sound technology
Plastics industry

Product features

Last Update (21.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 10 TBFH-LB

Cable coupler hood, high version
Single lever
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

LAPP

EPIC® H-B 10 TBFH-LB

PRODUCT INFORMATION

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: cable coupler hood (1 straight cable entry, single lever, high version)					
70042400	H-B 10 TBFH-LB 21	-	21	yes	10
70042600	H-B 10 TBFH-LB 29	-	29	yes	10
79042400	H-B 10 TBFH-LB M25	25	-	-	10
79042600	H-B 10 TBFH-LB M32	32	-	-	10

Last Update (21.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16