EPIC® H-B 10 TBFH

Housing design H-B. The industry standard.

The robust high metal housing consists of 2 double levers and a direct cable entry and is suitable for use in the plastics industry.

Info
More interior space for wiring
Double lever version with 2 levers for increased safety



Supplementary automation components from Lapp

Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits
The smallest housing with single and double lever. The right housing is available for every application

Application range
Plant engineering
Light & sound technology
Plastics industry

Product features
Cable coupler hood, high version

Last Update (01.01.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 10 TBFH

Dual levers
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2026 Lapp Group - Technical changes reserved

EPIC® H-B 10 TBFH

Article number	Article description	M	Packaging unit
79040400	H-B 10 TBFH M25	25	10
79040600	H-B 10 TBFH M32	32	10

Last Update (01.01.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16