EPIC® H-A 16 SGR-LB

These connectors are attractive because of their compact housing.

The robust metal housing with its compact design is suitable for applications with a high number of contacts such as in electronic laboratories.

Info
Protection rating UL50E tested





Waterproof

Robust

Mechanical resistance

Mechanical and plant engineering

Benefits
Small and compact, for applications with high number of contacts

Application range
Machine and equipment manufacturing
Control engineering
Electronic laboratory

Product features
Surface-mount base
Single lever
1 cable entry

Last Update (02.10.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-A 16 SGR-LB

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2025 Lapp Group - Technical changes reserved

EPIC® H-A 16 SGR-LB

Article number	Article description	M
19567100	H-A 16 SGR-LB M20	20
19567000	H-A 16 SGR-LB M25	25

Last Update (02.10.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16