

EPIC® H-A 16 TS


These connectors are attractive because of their compact housing.

The robust small metal housing is ideal for use in applications requiring a high number of contacts.

Info

Non-slip ridges for comfortable disconnecting

Protection rating UL50E tested



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Small and compact, for applications with high number of contacts

Application range

Machine and equipment manufacturing

Control engineering

Electronic laboratory

Product features

Hood, low version

Bolts for single lever

Side cable entry

Versions with neck

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-A 16 TS

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-A 16 TS

Article number	Article description	M	PG	Neck	Pieces / PU
H-A housing: hood (side cable entry, bolts for single lever)					
10564000	H-A 16 TS 16	-	16	yes	5
10564500	H-A 16 TS 21	-	21	yes	5
19564000	H-A 16 TS M20	20	-	yes	5
19564500	H-A 16 TS M25	25	-	yes	5