EPIC® H-B 10 TSH-RO

Housing design H-B. The industry standard.

The universal high metal housing has pivots for a single lever and a side cable entry. It is suitable for use in the plastics industry.

Info

Non-slip ridges for comfortable disconnecting
More interior space for wiring
Protection rating UL50E tested





Supplementary automation components from Lapp

Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits

The smallest housing with single and double lever. The right housing is available for every application

Application range

Plant engineering
Light & sound technology
Plastics industry

Product features

©2025 Lapp Group - Technical changes reserved

EPIC® H-B 10 TSH-RO

Hood, high version
Reels for single lever
Side cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2025 Lapp Group - Technical changes reserved

EPIC® H-B 10 TSH-RO

Article number	Article description	M	Packaging unit
79054200	H-B 10 TSH-RO M25	25	10
79054400	H-B 10 TSH-RO M32	32	10

Last Update (06.10.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.