

## EPIC® H-A 16 TSH

These connectors are attractive because of their compact housing.

The small compact metal housing with or without a neck has a side cable entry and is suitable for use in control systems.

### Info

Non-slip ridges for comfortable disconnecting

More interior space for wiring

Protection rating UL50E tested



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### Benefits

Small and compact, for applications with high number of contacts

### Application range

Machine and equipment manufacturing

Control engineering

Electronic laboratory

### Product features

Hood, high version

Bolts for single lever

Side cable entry

Last Update (05.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-A 16 TSH

Versions with / without neck

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-A 16 TSH**

Article number	Article description	M	PG	Neck	Pieces / PU
H-A housing: hood (side cable entry, bolts for single lever, high version)					
70492200	H-A 16 TSH 16	-	16	yes	5
70492400	H-A 16 TSH 21	-	21	yes	5
79492200	H-A 16 TSH M20	20	-	-	5
79492400	H-A 16 TSH M25	25	-	-	5

Last Update (05.06.2023)

©2023 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16