

## EPIC® H-A 3 AGS

Innovative metal and plastic housing design

The robust angular housing for placement in rectangular connectors can be used, for example, in electronic laboratories.

### Info

Lightweight, chemically resistant plastic housing

Protection rating UL50E tested



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### Benefits

Housing in plastic or metal version for safe connections in the smallest possible space

### Application range

Machine and equipment manufacturing

Control engineering

Electronic laboratory

### Product features

H-A case: Wall base

1 lever

Angled version

Included: flat gasket

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-A 3 AGS

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated zinc die-casting, grey Lever: zinc-plated steel Sealing: NBR Housing: grey thermoplastic, black Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-A 3 AGS**

Article number	Article description	M	Material	Colour	Pieces / PU
H-A housing: panel-mount base (angled)					
10423500	H-A 3 Mags	AG	Zinc die-casting	grey	10
10423100	H-A 3 Ags	AG	Thermoplastic	black	10
10423000	H-A 3 Ags	AG	Thermoplastic	grey	10

## EPIC® H-A 3 AGS

