

## EPIC® H-B 16 TBFH

Housing design H-B. The industry standard.

The robust metal housing consists of 2 double levers and a direct cable entry and is not only the ideal solution for application within the plastics industry.

### Info

- More interior space for wiring
- Double lever version with 2 levers for increased safety
- Protection rating UL50E tested



Waterproof



Robust



Mechanical resistance



Mechanical and plant engineering



Kompletterande automationskomponenter från Lapp

### Benefits

The housing standard. Wide choice for all applications

### Application range

- Plant engineering
- Plastics industry
- Light & sound technology

Last Update (05.07.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-B 16 TBFH

### Product features

Cable coupler hood, high version  
Dual levers  
Straight cable entry  
Versions with / without neck

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-B 16 TBFH**

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: cable coupler hood (straight cable entry, double lever, high version)					
70090200	H-B 16 TBFH 21	-	21	yes	5
70090400	H-B 16 TBFH 29	-	29	yes	5
79090200	H-B 16 TBFH M25	25	-	-	5
79090400	H-B 16 TBFH M32	32	-	-	5
79090401	H-B 16 TBFH 2xM32	2 x 32	-	-	5

Last Update (05.07.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16