

## EPIC® H-B 16 TG

Housing design H-B. The industry standard.

The robust housing for rectangular connectors with a direct cable entry is suitable for use in lighting and sound systems.

### Info

Non-slip ridges for comfortable disconnecting

High version: More interior space for wiring

Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### Benefits

The housing standard. Wide choice for all applications

### Application range

Plant engineering

Light & sound technology

Plastics industry

### Product features

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® H-B 16 TG

Hood, low version  
Bolts for double lever  
Straight cable entry  
Versions with / without neck

### Technical Data

|                        |  |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC000437<br>ETIM 5.0 Class-Description: Housing for industrial connectors |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC000437<br>ETIM 6.0 Class-Description: Housing for industrial connectors |
| Material:              | Housing: powder-coated aluminium alloy, grey<br>Lever: zinc-plated steel<br>Sealing: NBR     |
| Protection rating:     | IP 65 (latched)  |
| VDE-tested:            | Certified production control: VDE-REG. no.: B437<br>UL-tested:<br>UL File Number: E75770     |
| Temperature range:     | -40 °C to +100 °C, short-term up to +125 °C  |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® H-B 16 TG**

| Article number   | Article description | M  | PG | Neck | Pieces / PU |
|--|---------------------|----|----|------|-------------|
| H-B housing: hood (straight cable entry, bolts for double lever) |                     |    |    |      |             |
| 10080000   | H-B 16 TG 21        | -  | 21 | yes  | 5           |
| 10090000   | H-B 16 TG 29        | -  | 29 | yes  | 5           |
| 19080000   | H-B 16 TG M25       | 25 | -  | -    | 5           |
| 19090000   | H-B 16 TG M32       | 32 | -  | -    | 5           |