

EPIC® H-B 16 TGH 2X

Housing design H-B. The industry standard.


The robust high metal housing with a direct cable entry is suitable for use in investment construction.

Info

Non-slip ridges for comfortable disconnecting

For easy introduction of two cables

NEMA 250, UL50E: 12, 4 (latched)



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

The housing standard. Wide choice for all applications

More interior space for wiring

Application range

Plant engineering

Light & sound technology

Plastics industry

EPIC® H-B 16 TGH 2X

Product features

Hood, high version
Bolts for double lever
2 straight cable entries
Versions without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 16 TGH 2X

Article number	Article description	M	Pieces / PU
H-B housing: hood (2 straight cable entries, bolts for double lever, high version)			
44422018	H-B 16 TGH 2XM25	2 x 25	5
79128600	H-B 16 TGH 2XM32	2 x 32	5