EPIC® H-B 10 AD-BO

Housing design H-B. The industry standard.

The robust metal housing with pivots for a direct lever and a seal is suitable for use in the plastics industry or investment construction.

Info

Metal lid with sturdy hinge
Protection rating UL50E tested



Supplementary automation components from Lapp

Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits

The smallest housing with single and double lever. The right housing is available for every application

Application range

Plant engineering
Light & sound technology
Plastics industry

Product features

©2026 Lapp Group - Technical changes reserved

EPIC® H-B 10 AD-BO

H-A case: Wall base
Bolts for double lever
Metal cover
Included: flat gasket

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) IP 40 (cover closed) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2026 Lapp Group - Technical changes reserved

EPIC® H-B 10 AD-BO

Article number	Article description	M	Packaging unit
H-B housing: panel-mount base (cover, bolts for double lever)			
10033000	H-B 10 AD-BO	AG	10

©2026 Lapp Group - Technical changes reserved