EPIC® H-B 24 TBFH

Housing design H-B. The industry standard.

The universal metal housing with 2 double levers and a direct cable entry is able to withstand temperatures of approximately +125 degrees for a short period.

Info

More interior space for wiring
Double lever version with 2 levers for increased safety
Protection rating UL50E tested



Supplementary automation components from Lapp

Mechanical and plant engineering

Mechanical resistance

Robust

Waterproof

Benefits

Safe fixing with 4 screws
Casted neck for easy assembly of the cable gland

Application range

Plant engineering
Light & sound technology
Plastics industry

Last Update (02.06.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 24 TBFH

Product features

Cable coupler hood, high version
Dual levers
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2026 Lapp Group - Technical changes reserved

LAPP

EPIC® H-B 24 TBFH

PRODUCT INFORMATION

Article number	Article description	M	Packaging unit
79140400	H-B 24 TBFH M25	25	5
79140600	H-B 24 TBFH M32	32	5

©2026 Lapp Group - Technical changes reserved