EPIC® H-B 48 TS

Housing design H-B for 2 inserts.

The robust connector housing consists of a side cable entry and pivots for a single lever and can be used, for example, in investment construction.



Benefits
The large, robust housing for two inserts in one connector. Power and data in a single connector

Application range
Plant engineering
Plastics industry

Product features
Hood
Bolts for single lever
Side cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (31.05.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 48 TS

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (31.05.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 48 TS

Article number	Article description	M	Packaging unit
19158000	H-B 48 TS M32	32	1
19159000	H-B 48 TS M40	40	1
19160000	H-B 48 TS M50	50	1

Last Update (31.05.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16