

## EPIC® MH 1.0mm contacts machined

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

-

### Info

Machined gold plated contacts with 1mm diameter for EPIC® MH Gigabit module  
Gold-plated contacts for low transfer resistance



### Benefits

Machined gold plated contacts with 1mm diameter for EPIC® MH Gigabit module  
Gold-plated contacts for low transfer resistance

### Application range

Mechanical and plant engineering  
Robotics industry  
Renewable energy  
Railway applications / vehicle construction

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000796 ETIM 5.0 Class-Description: Contact for industrial connectors
Stripping length (mm):	4.2 ± 0.5mm
Material:	brass gold plated CuZn / Au
Cycle of mechanical operation:	500

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® MH 1.0mm contacts machined**

Article number	Article description	Contact type	Conductor cross-section AWG	Pieces / PU
44423285	EPIC® MH SCEM AU 0.09 - 0.25sqmm D=1.0	male	28.0 - 24.0	100
44423286	EPIC® MH BCEM AU 0.09 - 0.25sqmm D=1.0	female	28.0 - 24.0	100
44423287	EPIC® MH SCEM AU 0.13 - 0.33sqmm D=1.0	male	26.0 - 22.0	100
44423288	EPIC® MH BCEM AU 0.13 - 0.33sqmm D=1.0	female	26.0 - 22.0	100
44423289	EPIC® MH SCEM AU 0.25 - 0.52sqmm D=1.0	male	24.0 - 20.0	100
44423290	EPIC® MH BCEM AU 0.25 - 0.52sqmm D=1.0	female	24.0 - 20.0	100

Last Update (13.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16