


## EPIC® H-B 48 SGR-LB

Housing design H-B for 2 inserts.

The robust housing for two inserts consists of a single lever and a cable entry and is suitable for use in the plastics industry.



### Benefits

The large, robust housing for two inserts in one connector. Power and data in a single connector  
M40 housing extension on M50 with SKINTOP 53112083 possible (clamping range 27 - 35 mm)

### Application range

Plant engineering  
Plastics industry

### Product features

Surface-mount base  
Single lever  
1 cable entry

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material:

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating:

IP 65 (latched)

Temperature range:

-40°C to +100°C, short-term up to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (17.02.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16



## EPIC® H-B 48 SGR-LB

Article number	Article description	M	PG	Packaging unit
H-B housing: surface-mount base (1 cable entry, single lever)				
10165000	H-B 48 SGR 29	-	29	1
19165000	H-B 48 SGR M32	32	-	1
19165100	H-B 48 SGR M40	40	-	1

Last Update (17.02.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16