


EPIC® H-B 48 TS

Housing design H-B for 2 inserts.

The robust connector housing consists of a side cable entry and pivots for a single lever and can be used, for example, in investment construction.



Benefits

The large, robust housing for two inserts in one connector. Power and data in a single connector

Application range

Plant engineering
Plastics industry

Product features

Hood
Bolts for single lever
Side cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (10.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 48 TS

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 48 TS

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (side cable entry, bolts for single lever)					
10158000	H-B 48 TS 29	-	29	yes	1
10159000	H-B 48 TS 36	-	36	yes	1
10159200	H-B 48 TS 36	-	36	-	1
10160000	H-B 48 TS 42	-	42	yes	1
19158000	H-B 48 TS M32	32	-	-	1
19159000	H-B 48 TS M40	40	-	-	1
19160000	H-B 48 TS M50	50	-	-	1

Last Update (10.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16