







EPIC® SOLAR 4 Splitter

Connector system for weatherproof cabling of photovoltaic systems

Info

4 mm connector system with double hook
 Splitter for parallel connection of photovoltaic modules



-  Solar Energy
-  Suitable for outdoor use
-  Voltage
-  Temperature-resistant
-  UV-resistant
-  Waterproof

Benefits

Splitter for parallel connection of PV-modules and strings
 Easy plug and play
 Fixing option for a clear installation with a Ø 5mm mounting hole

Application range

Photovoltaic plants
 Crystalline and thin-film constructions
 Solartracker

Product features

Mateable with EPIC® SOLAR 4 THIN, EPIC® SOLAR 4PLUS, EPIC® SOLAR 4

EPIC® SOLAR 4 Splitter

Splitter MFF 1x connection male, 2x connection female
Splitter MFF 1x connection female, 2x connection male

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002635 ETIM 5.0 Class-Description: Circular connector (industrial connector)
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002635 ETIM 6.0 Class-Description: Circular connector (industrial connector)
Rated voltage (V):	1000 V AC/DC
Rated impulse voltage:	8 kV
Rated current (A):	30 A
Pollution degree:	3
Protection rating:	IP65/IP67
Cycle of mechanical operation:	100
Protection class:	II
Temperature range:	-40 °C ... +85 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® SOLAR 4 Splitter

Article number	Article designation	PU
EPIC® SOLAR 4 Splitter		
44428226	EPIC® SOLAR 4 Splitter MFF	25
44428227	EPIC® SOLAR 4 Splitter FMM	25

Last Update (08.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® SOLAR 4 Splitter

