

DYMO® XTL 300 / 500

Uncomplicated, time-saving and versatile labeling device for mobile use



Assembly time



Low weight



Space requirement

Benefits

- Label printer recognizes automatically inserted label
- Intuitive handling through integrated labelling applications
- Time-saving by pre-sized labels
- Accurate print preview
- Integrated rubber bumpers help prevent damage from accidental drops and falls

Application range

- Marking of cables, wires and components
- Resistant to UV-light, oil, humidity and chemicals

Product features

- Thermal transfer printing technology
- XTL 500: max. label width 54mm, touchscreen, automatic cutter

Norm references / Approvals

- Vinyl tapes & laminated wrapping labels:
- UL recognized as a component according to UL 969
- File Number: MH48389

Note

Free DYMO ID software for PC connection (available at www.dymo.com) for easy transfer of labels

Last Update (01.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

DYMO® XTL 300 / 500

Included

Kit contains 1 DYMO 500 (incl. labels VIN 54BK / WH and LAM 38x39 WH), charging adapter, USB cable, Li-Ion battery, lanyard and instruction in a hard case

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 Class-Description: Labelling material

Material:

Vinyl tapes and wrapping labels: Vinyl

Shrink tube: Polyolefin (flame retardant UL224), shrink ratio 3:1

Temperature range:

-40 °C to +60 °C

Note

DYMO® is a registered trademark of Sanford GmbH, a Newell Rubbermaid Company

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

DYMO® XTL 300 / 500

Article number	Article designation	Width (mm)	For cable Ø (mm)	Colour of tape	Printer	m / PU
83257107	DYMO XTL KIT 500	-	-	-	-	-
Vinyl tapes						
83257146	DYMO XTL VIN 12BK/TR	12	-	transparent	XTL 300/500	7
83257156	DYMO XTL VIN 12BK/WH	12	-	white	XTL 300/500	7
83257157	DYMO XTL VIN 19BK/WH	19	-	white	XTL 300/500	7
83257160	DYMO XTL VIN 54BK/WH	54	-	white	XTL 500	7
83257170	DYMO XTL VIN 54WH/RD	54	-	red	XTL 500	7
83257180	DYMO XTL VIN 54BK/YE	54	-	yellow	XTL 500	7
Shrink tube tapes						
83257214	DYMO XTL SHRINK 6-2700BK/WH	6	2.0 - 6.0	white	XTL 300/500	2.7
83257215	DYMO XTL SHRINK 12-2700BK/WH	12	4.0 - 12.0	white	XTL 300/500	2.7
83257216	DYMO XTL SHRINK 24-2700BK/WH	24	8.0 - 24.0	white	XTL 300/500	2.7

Last Update (01.05.2025)


©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

DYMO® XTL 300 / 500



Last Update (01.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16