


## FLEXIMARK® Shrink mark

FLEXIMARK® Flat Heat shrinkable tubing for cable marking can be easily printed with our software and a thermal transfer printer.



Wind Energy



Good chemical resistance



Flame-retardant

### Benefits

Flat shrink tube that can be cut individually to the required length

### Application range

For cable marking

For applications where space is tight

Protection of the cable insulation

Especially suitable for repair purposes

### Norm references / Approvals

UL 224 certified

### Note

Easy to print via FLEXIMARK® software Flexisoft and FLEXIMARK® thermal transfer printer SQUIX, EOS5 or EOS2

Recommended ribbon:

Text colour black: FTI-X 60-300 BK (article no. 83260206),

Text colour white: FTI-X 55-300 WH (article no. 83260260)

Use the EOS5 printer with additional cutter for cutting, use the SQUIX printer with additional perforation cutter for perforating the shrink tubes

With customized print: see product FLEXIMARK® Shrink tube FCC

### Included

Delivered as a roll of labels

### Technical Data

Last Update (29.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FLEXIMARK® Shrink mark

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Heat-shrink tubing
Classification ETIM 6:	ETIM 6.0 Class-Description: Shrink tubing
Colour delivered:	Black, yellow and white
Material:	Polyolefin Shrinking ratio: 3:1
Temperature range:	-55°C to +135°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

**FLEXIMARK® Shrink mark**

Article number	Article designation	Colour	Shrinkage range (mm)	PU (m)	PU
83251670	FLEXIMARK® Shrinking tube 3/1 BK	black	1.0 - 3.0	30	1
83251671	FLEXIMARK® Shrinking tube 6/2 BK	black	2.0 - 6.0	25	1
83251672	FLEXIMARK® Shrinking tube 9/3 BK	black	3.0 - 9.0	20	1
83251673	FLEXIMARK® Shrinking tube 12/4 BK	black	4.0 - 12.0	20	1
83251674	FLEXIMARK® Shrinking tube 18/6 BK	black	6.0 - 18.0	20	1
83251680	FLEXIMARK® Shrinking tube 3/1 YE	yellow	1.0 - 3.0	30	1
83251681	FLEXIMARK® Shrinking tube 6/2 YE	yellow	2.0 - 6.0	25	1
83251682	FLEXIMARK® Shrinking tube 9/3 YE	yellow	3.0 - 9.0	20	1
83251683	FLEXIMARK® Shrinking tube 12/4 YE	yellow	4.0 - 12.0	20	1
83251684	FLEXIMARK® Shrinking tube 18/6 YE	yellow	6.0 - 18.0	20	1
83251690	FLEXIMARK® Shrinking tube 3/1 WH	white	1.0 - 3.0	30	1
83251691	FLEXIMARK® Shrinking tube 6/2 WH	white	2.0 - 6.0	25	1
83251692	FLEXIMARK® Shrinking tube 9/3 WH	white	3.0 - 9.0	20	1
83251693	FLEXIMARK® Shrinking tube 12/4 WH	white	4.0 - 12.0	20	1
83251694	FLEXIMARK® Shrinking tube 18/6 WH	white	6.0 - 18.0	20	1

Last Update (29.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16