

FLEXIMARK® Stainless steel character holders NM

FLEXIMARK® Character holder NM for assembly of characters made of acid-proof stainless steel for cable and component marking in the electrical industry

Info

PR 1 NM 7 included in FLEXIMARK® sample bag (article no. M3251010)



Suitable for outdoor use



Good chemical resistance



Cold-resistant



Corrosion-resistant



Acid-resistant



UV-resistant

Benefits

Quick, simple and permanent marking on site

Application range

Cable and component marking system

For mounting MR stainless steel characters

Markers could be used in any industry with a demanding environment (e.g. oil & gas, railways)

Norm references / Approvals

Achilles JQS certified

Note

Mounted with cable ties (maximum 7.9 mm width) or screws (up to 3 mm Ø)

Last Update (14.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Stainless steel character holders NM**Technical Data**

| | |
|------------------------|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001288 ETIM 6.0 Class-Description: Labelling material |
| Dimensions: | The tolerance of the dimensions is +/-1,5 mm. |
| Info: | Height: approx. 11 mm Screw hole Ø: 3 mm |
| Material: | Acid resistant stainless steel EN 1.4404 (SS2348, AISI 316L) |
| Temperature range: | -80 °C to +500 °C |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Stainless steel character holders NM

| Article number | Article designation | Length (mm) | Max. Amount of Characters | Markers / PU | PU |
|----------------|----------------------|-------------|---------------------------|--------------|----|
| 83254214 | FLEXIMARK® PR10 NM4 | 48.0 | 6 | 50 | 1 |
| 83254213 | FLEXIMARK® PR10 NM5 | 60.0 | 8 | 50 | 1 |
| 83254212 | FLEXIMARK® PR10 NM7 | 84.0 | 12 | 50 | 1 |
| 83254211 | FLEXIMARK® PR10 NM9 | 108.0 | 16 | 50 | 1 |
| 83254215 | FLEXIMARK® PR10 NM11 | 176.0 | 26 | 50 | 1 |
| 83254210 | FLEXIMARK® PR10 NM24 | 288.0 | 46 | 50 | 1 |

Last Update (14.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16