# EPIC® MH 10.0mm Contacts

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

-

## Info

Crimping contacts for maximum cross sections and currents
Modular connector system, mateable with the market standard

Supplementary automation components from Lapp

Mechanical and plant engineering

Rail

Wind Energy

Suitable for outdoor use

Robust

Voltage

## Benefits

Male and female contacts with silver plating
Crimping with Klauke D 22 and HD 13 series
Cross section: 25, 35, 50, 70 and 95 mm²

## Application range

Mechanical engineering
Renewable energy
Test equipment building

Last Update (05.04.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

# EPIC® MH 10.0mm Contacts

Plant engineering
Railway applications / vehicle construction

## Technical Data

| | |
|---|---|
| Termination methods: | Crimp termination: 25mm² ... 95mm² |
| Stripping length (mm): | 23 |
| Material: | brass silver plated CuZn / Ag |
| Cycle of mechanical operation: | 500 |

## Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (05.04.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

LAPP

# EPIC® MH 10.0mm Contacts

PRODUCT INFORMATION

| Article number | Article description | Contact type | Connection cross section ($mm^2$) | Pieces / PU |
|---|---|---|---|---|
| EPIC® MH 10.0mm operating contacts | | | | |
| 44423330 | EPIC® MH SCEM AG 25sqmm D=10.0 | male | 25 | 10 |
| 44423331 | EPIC® MH BCEM AG 25sqmm D=10.0 | female | 25 | 10 |
| 44423332 | EPIC® MH SCEM AG 35sqmm D=10.0 | male | 35 | 10 |
| 44423333 | EPIC® MH BCEM AG 35sqmm D=10.0 | female | 35 | 10 |
| 44423334 | EPIC® MH SCEM AG 50sqmm D=10.0 | male | 50 | 10 |
| 44423335 | EPIC® MH BCEM AG 50sqmm D=10.0 | female | 50 | 10 |
| 44423336 | EPIC® MH SCEM AG 70sqmm D=10.0 | male | 70 | 10 |
| 44423337 | EPIC® MH BCEM AG 70sqmm D=10.0 | female | 70 | 10 |
| 44423338 | EPIC® MH SCEM AG 95sqmm D=10.0 | male | 95 | 10 |
| 44423339 | EPIC® MH BCEM AG 95sqmm D=10.0 | female | 95 | 10 |

Last Update (05.04.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16