

## EPIC® SOLAR 4 Splitter

Connector system for weatherproof cabling of photovoltaic systems

### Info

4 mm connector system with double hook

Splitter for parallel connection of photovoltaic modules



Solar Energy



Suitable for outdoor use



Voltage



Temperature-resistant



UV-resistant



Waterproof

### Benefits

Splitter for parallel connection of PV-modules and strings

Easy plug and play

Fixing option for a clear installation with a Ø 5mm mounting hole

### Application range

Photovoltaic plants

Crystalline and thin-film constructions

Solartracker

### Product features

Mateable with EPIC® SOLAR 4 THIN, EPIC® SOLAR 4PLUS, EPIC® SOLAR 4

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® SOLAR 4 Splitter

Splitter MFF 1x connection male, 2x connection female  
Splitter MFF 1x connection female, 2x connection male

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002635 ETIM 5.0 Class-Description: Circular connector (industrial connector)
Classification ETIM 6:	ETIM 6.0 Class-ID: EC002635 ETIM 6.0 Class-Description: Circular connector (industrial connector)
Rated voltage (V):	1000 V AC/DC
Rated impulse voltage:	8 kV
Rated current (A):	30 A
Pollution degree:	3
Protection rating:	IP65/IP67
Cycle of mechanical operation:	100
Protection class:	II
Temperature range:	-40 °C ... +85 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

## EPIC® SOLAR 4 Splitter

Article number	Article designation	PU
EPIC® SOLAR 4 Splitter		
44428226	EPIC® SOLAR 4 Splitter MFF	25
44428227	EPIC® SOLAR 4 Splitter FMM	25

## EPIC® SOLAR 4 Splitter

