


FLEXIMARK® Cablelabel LFL

FLEXIMARK® Cablelabel LFL for marking cables with cable ties (one- or two sided fastening possibility). Text can be printed on the labels with our marking software and commercial laser printers.

Info

LFL2H 9.9-26 included in FLEXIMARK® sample bag (article no. M3251010)



Good chemical resistance



Halogen-free



UV-resistant

Benefits

Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)
Printable on both sides

Application range

For cable marking
Can be mounted directly on the cable together with plastic cable ties
No character holder necessary

Note

Can be printed with the FLEXIMARK® Software and a commercial laser printer
Insert sheet in manual paper feed compartment
Optimum printing results from laser printers are achieved with straight sheet feed-in

Included

Perforated DIN A4 / A5 sheets

Product Make-up

One (LFL1H) or two-sided (LFL2H) fastening with cable ties (up to 4.5 mm in width)

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Cablelabel LFL

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001530 ETIM 5.0 Class-Description: Cable coding system
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001530 ETIM 6.0 Class-Description: Cable coding system
Colour delivered:	Yellow/White (can be printed on both sides)
Material:	Halogen-free polyester Thickness: 0.175 mm
Temperature range:	-40 °C to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Cablelabel LFL

Article number	Article designation	Colour	Width x length (mm)	Labelling surface (mm)	Markers / PU	PU
83254750	FLEXIMARK® Label LFL2H 9.9-26 YEWH	yellow/white	9.9 x 48.0	9.9 x 26.0	400	1
83254760	FLEXIMARK® Label LFL1H 9.9-35 YEWH	yellow/white	9.9 x 48.0	9.9 x 35.0	400	1
83254765	FLEXIMARK® Label LFL2H 66-9.9 YEWH	yellow/white	9.9 x 89.0	9.9 x 66.0	560	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16