




## FLEXIMARK® Flexiprint TF

FLEXIMARK® Flexiprint TF are markers for single core marking and marking of glass fibre cables, easy and quick to install.

### Info

TF1 included in FLEXIMARK® sample bag (article no. M3251010)



Good chemical resistance



Halogen-free



Assembly time



UV-resistant

### Benefits

Resistant to chemicals, UV-light, moisture and oils (diesel oil, basic cleaning agent, sea water, ethanol,...)  
Easy to install

### Application range

For single core marking  
Marking of optical fibre cables  
Marking before assembly  
For cable cross-sections over 16.00 mm<sup>2</sup>, cable ties can be used for installing single markers

### Note

Can be printed with the FLEXIMARK® Software and the FLEXIMARK® Thermal transfer printer SQUIX or EOS5  
Recommended ribbon: R71 110-360 resin BK (article no. 83259609)  
Normal version: Up to 7 characters  
L version (e.g. LF1L): Up to 15 characters

### Included

Delivered as a roll of labels

Last Update (22.10.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FLEXIMARK® Flexiprint TF

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001288 ETIM 6.0 Class-Description: Labelling material
Colour delivered:	yellow also available in green, blue and red
Material:	Halogen-free polyester Thickness: 0.175 mm
Temperature range:	-40°C to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

**FLEXIMARK® Flexiprint TF**

Article number	Article designation	Colour	For mm <sup>2</sup>	A mm	B (mm)	C (mm)	D (mm)	E (mm)	Markers / PU	PU
Small packaging										
83255011	FLEXIMARK® Flexiprint TF0 WH600	white	0.25 - 0.75	22.9	5.2	3.9	13.1	2.4	600	1
83255012	FLEXIMARK® Flexiprint TF1 WH600	white	0.75 - 1.5	23	5.2	4.9	11.2	3.5	600	1
83255013	FLEXIMARK® Flexiprint TF1B WH600	white	1.5 - 2.5	25	5.7	5.9	11.2	4.2	600	1
83255014	FLEXIMARK® Flexiprint TF2 WH600	white	2.5 - 6.0	26	7	6.5	11	5.5	600	1
83255015	FLEXIMARK® Flexiprint TF3 WH600	white	6.0 - 16.0	41	11	10.5	17	8.4	200	1
Large packaging										
83254372	FLEXIMARK® Flexiprint TF0 YE	yellow	0.25 - 0.75	22.9	5.2	3.9	13.1	2.4	2000	1
83254378	FLEXIMARK® Flexiprint TF1 YE	yellow	0.75 - 1.5	23	5.2	4.9	11.2	3.5	2000	1
83254354	FLEXIMARK® Flexiprint TF1L WH	yellow	0.75 - 1.5	34	5.2	5	22	3.5	2000	1
83254374	FLEXIMARK® Flexiprint TF1B YE	yellow	1.5 - 2.5	25	5.7	5.9	11.2	4.2	2000	1
83254359	FLEXIMARK® Flexiprint TF1BL YE	yellow	1.5 - 2.5	36	5.7	6	22	4.2	2000	1
83254375	FLEXIMARK® Flexiprint TF2 YE	yellow	2.5 - 6.0	26	7	6.5	11	5.5	2000	1
83254376	FLEXIMARK® Flexiprint TF3 YE	yellow	6.0 - 16.0	41	11	10.5	17	8.4	1000	1
83254365	FLEXIMARK® Flexiprint TF0 WH	white	0.25 - 0.75	22.9	5.2	3.9	13.1	2.4	2000	1

Last Update (22.10.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.  
 PN 0456 / 02\_03\_16

**FLEXIMARK® Flexiprint TF**

Article number	Article designation	Colour	For mm <sup>2</sup>	A mm	B (mm)	C (mm)	D (mm)	E (mm)	Markers / PU	PU
83254366	FLEXIMARK® Flexiprint TF1 WH	white	0.75 - 1.5	23	5.2	4.9	11.2	3.5	2000	1
83254355	FLEXIMARK® Flexiprint TF1L WH	white	0.75 - 1.5	34	5.2	5	22	3.5	2000	1
83254367	FLEXIMARK® Flexiprint TF1B WH	white	1.5 - 2.5	25	5.7	5.9	11.2	4.2	2000	1
83254360	FLEXIMARK® Flexiprint TF1BL WH	white	1.5 - 2.5	36	5.7	6	22	4.2	2000	1
83254368	FLEXIMARK® Flexiprint TF2 WH	white	2.5 - 6.0	26	7	6.5	11	5.5	2000	1
83254369	FLEXIMARK® Flexiprint TF3 WH	white	6.0 - 16.0	41	11	10.5	17	8.4	1000	1

Last Update (22.10.2019)

©2019 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

 You can find the current technical data in the corresponding data sheet.  
 PN 0456 / 02\_03.16