

NA2XS(F)2Y

Longitudinally water-tight PE medium voltage cable with aluminium conductor

NA2XS(F)2Y, VDE, PE medium voltage cable acc. VDE 0276-620, with aluminium conductor, longitudinally water-tight, for fixed installation

Info

3 voltage classes: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV
With aluminium conductor



Suitable for outdoor use



Mechanical resistance



UV-resistant



Waterproof

Application range

Power and control cable for fixed installation in the following applications:

In water, in ground, outdoors and indoors

In cable trays for power stations, industry, and distribution networks

Also suitable for applications where longitudinal water propagation inside the cable should be avoided.

Burial without additional, suitable underground protection according to HD 620/VDE 0276-620 - Part 10-C (point 4): normal minimum installation depth 0.6 m, but at least 0.8 m under roads

Product features

Suitable for installation or operation under high mechanical stress due to the PE-sheath

Current rating according to HD 620/VDE 0276-620, Part 10-C, Table 7 (buried at +20 °C ground temperature according to HD 620/VDE 0276-620, Part 10-C, point 5) for routing underground and Table 8 (in the air at an air temperature of +30 °C according to HD 620/VDE 0276-620, Part 10-C, point 5) when used outdoors; but always taking into consideration corrections/reductions to the

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

NA2XS(F)2Y

current rating that may be necessary according to VDE 0298-4, and VDE 0298-4 (also refer to the catalogue appendix T12) for installation in and on buildings

Norm references / Approvals

HD 620/ VDE 0276-620

Product Make-up

Aluminium conductor

Abbreviation "rm":

r = round conductor form;

m = multi-wire conductor

Core insulation: Cross-linked Polyethylen (XLPE)

Screen made of copper wires with one or two copper bond counter spiral longitudinally water-tight wrapping

Outer sheath: PE, black

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001140 ETIM 5.0 Class-Description: Medium voltage power cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001140 ETIM 6.0 Class-Description: Medium voltage power cable
Conductor stranding:	Multi-wire
Minimum bending radius:	Fixed installation: 15 x outer diameter
Nominal voltage:	U_0/U : 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV
Test voltage:	Depending on nominal voltage: 6/10 kV: 15 kV 12/20 kV: 30 kV 18/30 kV: 45 kV
Temperature range:	During installation: -40 °C to +70 °C Fixed installation: -40 °C to +90 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Aluminium price basis: excludes aluminium. Refer to catalogue appendix T17 for the application and definition of "Metal price basis" and "Metal index".

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

NA2XS(F)2Y

Article number	Number of cores and mm ² per conductor	Alu index (kg/km)	Outer diameter [mm]	Weight (kg/km)
6/10 (12) kV				
1552026	1 x 50 RM/16	145	25	617
38107610	1 x 70 RM/16	203	27	709
38107611	1 x 95 RM/16	276	28	805
38107612	1 x 120 RM/16	348	30	901
38801523	1 x 150 RM/25	435	31	1082
38106386	1 x 185 RM/25	537	33	1216
38801932	1 x 240 RM/25	696	35	1415
38802344	1 x 300 RM/25	870	37	1620
38107614	1 x 400 RM/35	1160	40	2024
38107615	1 x 400 RM/50	1160	40	2024
38107616	1 x 500 RM/35	1450	43	2369
38107617	1 x 630 RM/35	1827	47	2817
38107618	1 x 800 RM/35	2320	51	3381
38107619	1 x 1000 RM/35	2900	56	4100
12/20 (24) kV				
38107620	1 x 50 RM/16	145	29	768
38000155	1 x 70 RM/16	203	31	868
38000184	1 x 95 RM/16	276	32	975
1552028	1 x 120 RM/16	348	34	1079
38107621	1 x 150 RM/16	435	35	1268
3037568	1 x 150 RM/25	435	35	1268
1552029	1 x 185 RM /25	537	37	1413
38801987	1 x 240 RM/25	696	39	1626
38801756	1 x 300 RM/25	870	41	1845
38801724	1 x 400 RM/35	1160	44	2226
38801988	1 x 500 RM/35	1450	47	2599
38801986	1 x 630 RM/35	1827	51	3093
1552065	1 x 800 RM/35	2320	56	3727
38103208	1 x 1000 RM/35	2900	61	4450
18/30 (36) kV				
38000116	1 x 50 RM/16	145	34	981
38107622	1 x 70 RM/16	203	36	1085
38000476	1 x 95 RM/16	276	37	1211

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

NA2XS(F)2Y

Article number	Number of cores and mm ² per conductor	Alu index (kg/km)	Outer diameter [mm]	Weight (kg/km)
38107623	1 x 95 RM/35	396	37	1211
38106295	1 x 120 RM/16	348	39	1325
38105412	1 x 150 RM/25	435	40	1524
38106387	1 x 185 RM/25	537	42	1681
1552031	1 x 240 RM/25	696	44	1912
38105413	1 x 300 RM/25	870	46	2150
1552033	1 x 400 RM/35	1160	49	2550
1552045	1 x 500 RM/35	1450	52	2959
1552030	1 x 630 RM/35	1827	56	3498
38106514	1 x 800 RM/35	2320	61	4152

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16