

## HITRONIC® HUW Armoured Universal Cable

Universal cable with central loose tube, corrugated steel tape and non-metallic strain relief for applications with extended mechanical stress


HITRONIC® HUW armoured Universal cable, stranded loose tubes, corrugated steel tape, LSZH outer sheath  
J/A-DQ(ZN)(SR)H

### Info

CPR: Article number choice under [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)

For indoor and outdoor use

cable with corrugated steel tape (CST) for increased mechanical stress



 Ethernet



Halogen-free



Heat-resistant



Mechanical resistance



Low weight



Optimum strain relief



UV-resistant



Waterproof

### Benefits

Armouring provides excellent protection  
against high mechanical stress and rodents

Flame retardance makes it suitable for indoor and outdoor installations

Last Update (10.10.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## HITRONIC® HUW Armoured Universal Cable

Easy to install due to the compact design, high flexibility, robust sheath and small bending radii  
Water-resistant

### Application range

For indoor and outdoor use  
Campus backbone  
Industrial environments  
Methods of Deployment: empty plastic pipes, ducts and trays

### Product features

Outer sheath flame-retardant and halogen-free  
Central loose tube with up to 24 fibres  
Colour-coded fibres  
Longitudinal watertight  
Excellent rodent protection

### Product Make-up

Gel-filled loose tube  
Water-blocking reinforced glass yarn strain relief  
Corrugated steel tape armour  
LSZH outer sheath  
Colour: green (based on RAL 6018)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000034 ETIM 5.0 Class-Description: Fibre optic cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000034 ETIM 6.0 Class-Description: Fibre optic cable
Dimensions:	Primary coated fibre: 250µm Cable: see table
Core identification code:	Fibre colour code see data sheet
Fibre type:	GOF - Glass Optical Fibre
Standard designation:	A/J-DQ(ZN)(SR)H U-DQ(ZN)(SR)H
Optical values:	see data sheet
Optical fibre type:	Core material: glass Cladding material: glass
Permissible bending radius:	Static: $\geq 15 \times$ outer diameter Dynamic: $\geq 20 \times$ outer diameter
Permissible tensile force:	Fixed installation: 1500 N Short-term: 2000 N
Temperature range:	Fixed installation: -30°C to +70°C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

The cables can also be supplied as pre-terminated fibre optic trunks.

Last Update (10.10.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## HITRONIC® HUW Armoured Universal Cable

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.  
Available on request with Multimode OM4 fibres.

**HITRONIC® HUW Armoured Universal Cable**

Article number	Article designation	Fibre type	Number of fibres	Outer diameter [mm]	Weight (kg/km)
<b>Multimode G 50 OM4</b>					
27500404	HITRONIC® HUW1500 4G 50/125 OM4	50/125 OM4	4	9.6	88
27500408	HITRONIC® HUW1500 8G 50/125 OM4	50/125 OM4	8	9.6	88
27500412	HITRONIC® HUW1500 12G 50/125 OM4	50/125 OM4	12	9.6	88
27500424	HITRONIC® HUW1500 24G 50/125 OM4	50/125 OM4	24	9.6	88
<b>Multimode G 50 OM3</b>					
27500304	HITRONIC® HUW1500 4G 50/125 OM3	50/125 OM3	4	9.6	88
27500308	HITRONIC® HUW1500 8G 50/125 OM3	50/125 OM3	8	9.6	88
27500312	HITRONIC® HUW1500 12G 50/125 OM3	50/125 OM3	12	9.6	88
27500324	HITRONIC® HUW1500 24G 50/125 OM3	50/125 OM3	24	9.6	88
<b>Multimode G 50 OM2</b>					
27500204	HITRONIC® HUW1500 4G 50/125 OM2	50/125 OM2	4	9.6	88
27500208	HITRONIC® HUW1500 8G 50/125 OM2	50/125 OM2	8	9.6	88
27500212	HITRONIC® HUW1500 12G 50/125 OM2	50/125 OM2	12	9.6	88
27500224	HITRONIC® HUW1500 24G 50/125 OM2	50/125 OM2	24	9.6	88
<b>Multimode G 62.5 OM1</b>					
27500104	HITRONIC® HUW1500 4G 62.5/125 OM1	62.5/125 OM1	4	9.6	88
27500108	HITRONIC® HUW1500 8G 62.5/125 OM1	62.5/125 OM1	8	9.6	88
27500112	HITRONIC® HUW1500 12G 62.5/125 OM1	62.5/125 OM1	12	9.6	88
27500124	HITRONIC® HUW1500 24G 62.5/125 OM1	62.5/125 OM1	24	9.6	88
<b>Single-mode E 9 OS2</b>					
27500904	HITRONIC® HUW1500 4E 9/125 OS2	9/125 OS2	4	9.6	88
27500908	HITRONIC® HUW1500 8E 9/125 OS2	9/125 OS2	8	9.6	88

Last Update (10.10.2019)

©2019 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

**HITRONIC® HUW Armoured Universal Cable**

Article number	Article designation	Fibre type	Number of fibres	Outer diameter [mm]	Weight (kg/km)
	9/125 OS2				
27500912	HITRONIC® HUW1500 12E 9/125 OS2	9/125 OS2	12	9.6	88
27500924	HITRONIC® HUW1500 24E 9/125 OS2	9/125 OS2	24	9.6	88

Last Update (10.10.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16