

## ÖLFLEX® CRANE CF

Weather-resistant flat rubber cables with copper screening

ÖLFLEX® CRANE CF - Flat cable for outdoor use and crane applications/conveyour technology. Screened power and control rubber cable,  $U_0/U$ :300/500V

### Info

For outdoor cable trolley application  
EMC-compliant



Suitable for outdoor use



Cold-resistant



Oil-resistant



Interference signals



UV-resistant

### Benefits

Weather-resistant for harsh environmental conditions  
Flat cables need less space than round cables  
Smaller bending radii is possible  
Copper braiding screens the cable against electromagnetic interference

### Application range

In crane systems on building sites and shipyards for fixed installation, or for flexible use in

Last Update (14.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## ÖLFLEX® CRANE CF

cable trolley systems

Sewage treatment plants, steelworks and high rack facilities

The application profiles for ÖLFLEX® CRANE and ÖLFLEX® LIFT cables can be found in the appendix, selection table A3

As a lift control cable: max. 50 m suspension length

### Product features

Flame-retardant according IEC 60332-1-2

### Norm references / Approvals

Based on VDE 0250-809 (NGFLGÖU)

### Product Make-up

Conductors: Finely stranded bare copper

Core insulation: rubber compound

Individual core screening consist of

- plastic foil wrapping
- tin-plated copper braiding
- plastic foil wrapping

Outer sheath: special rubber compound

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000825 ETIM 5.0 Class-Description: Flat cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000825 ETIM 6.0 Class-Description: Flat cable
Core identification code:	Up to 5 cores: colour-coded according to VDE 0293-308, refer to Appendix T9 From 6 cores: black with white numbers
Conductor stranding:	Copper conductor according to VDE 0295/IEC 60228 up to 25 mm <sup>2</sup> : extra-fine wire, class 6 from 35 mm <sup>2</sup> : fine wire, class 5
Minimum bending radius:	Flexible use: 10 x cable thickness Fixed installation: 4 x cable thickness
Nominal voltage:	U0/U: 300/500 V
Test voltage:	2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Flexible use: -25 °C to +90 °C Fixed installation: -40 °C to +90 °C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (14.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**ÖLFLEX® CRANE CF**

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® CRANE CF**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer dimensions, width x height (mm)	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CRANE CF				
0041075	4.0 G 1.5	18.5 x 6.5	79	220
0041076	8.0 G 1.5	36.0 x 6.5	155	470
0041077	12.0 G 1.5	54.5 x 7.1	238	745
0041078	4.0 G 2.5	22.8 x 7.7	141	320

Last Update (14.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16