

NYCY

Fixed installation, direct burial; PVC cable with concentric, helical copper conductor and cross-conductive spiral

NYCY, <VDE>, PVC power cable acc. HD603 / VDE 0276-603, direct burial and fixed installation, building installation with concentric, helical copper conductor

Info

CPR: Article number choice under www.lappkabel.com/cpr

With concentric, helical copper conductor



Suitable for outdoor use

Benefits

Concentric conductor above all as PE

Application range

Power and control cable for fixed installation in the following applications:

For indoor and outdoor use

Burial without additional, suitable underground protection according to VDE standard HD 603/VDE 0276-603 - Part 3-G (point 4) governing PVC cables for direct burial: normal minimum installation depth 0.6 m, but at least 0.8 m under roads

In concrete with a temperature below the maximum cable operating temperature of +70 °C according to the VDE standard HD 603/VDE 0276-603 - Part 3-G (point 4) governing PVC cables for direct burial

Product features

Flame-retardant according IEC 60332-1-2

Current rating according to HD 603/VDE 0276-603, Part 3-G, Table 14 (buried at +20 °C ground temperature according to HD 603/VDE 0276-603, Part 3-G, point 5) for routing underground and Table 15 (in the air at an air temperature of +30 °C according to HD 603/VDE 0276-603, Part 3-G, point 5) when used outdoors; but always taking into consideration corrections/reductions to the current rating that may be necessary according to VDE 0298-4, and VDE 0298-4 (also refer to the catalogue appendix T12) for installation in and on buildings

Norm references / Approvals

Last Update (09.10.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

NYCY

HD 603/VDE 0276-603 for NYCY with 3 or 4 cores and the relevant additional concentric protective conductor
HD 627/VDE 0276-627 for NYCY as from 7 cores and with the additional, concentric protective conductor

Product Make-up

Bare copper wire conductor

Abbreviations "re", "rm", "se", "sm":

r = round conductor form;

s = sectorial conductor form;

e = single-wire conductor;

m = multi-wire conductor;

Core insulation: Based on PVC

Filling compound over the core assembly

Concentric, helical, outer conductor made of bare copper strands with inductance-reducing, cross-conductive copper bond counter spiral

Outer sheath: Based on PVC

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000057 ETIM 5.0 Class-Description: Low voltage power cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000057 ETIM 6.0 Class-Description: Low voltage power cable
Core identification code:	Up to 5 cores: colour-coded according to VDE 0293-308, refer to Appendix T9 From 6 cores: black with white numbers
Conductor stranding:	Single or multi-wire
Minimum bending radius:	Fixed installation: 12 x outer diameter
Nominal voltage:	U0/U: 0.6/1.0 kV
Test voltage:	4000 V
Temperature range:	During installation: -5 °C to +50 °C Fixed installation: -40 °C to +70 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: excluding copper. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
15503003	2 x 1,5re/1,5	14	52	245
15503103	3 x 1,5re/1,5	14	66	280
15503203	4 x 1,5re/1,5	15	81	302
1550330	7 x 1,5re/2,5	17	133	450
1550332	12 x 1,5re/2,5	20	205	580
1550337	24 x 1,5re/6	26	413	1100
15503113	3 x 2,5re/2,5	15	104	316
15503213	4 x 2,5re/2,5	16	128	360
1550350	7 x 2,5re/2,5	18	200	530
1550355	16 x 2,5re/6	23	451	950
15503223	4 x 4re/4	18	200	485
15503233	4 x 6re/6	19	297	616
1550299	2 x 2,5re/2,5	12.6	80	241
15503123	3 x 4re/4	15.3	161	384
1550313	3 x 6re/6	16.7	240	484
1550322	7 x 4re/4	18.7	315	621

Last Update (09.10.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16