

ÖLFLEX® LIFT N

Flexible at cold temperatures, PVC lift cables with supporting element

ÖLFLEX® LIFT N - PVC control cable with supporting element for conveyour/lift applications, 300/500V, highly flexible, class 6, outdoor application

Info

New Product, Follower of ÖLFLEX® LIFT



Suitable for outdoor use



Cold-resistant



Optimum strain relief



UV-resistant

Benefits

Special cable design for a long service life

Very flexible due to extra-fine wire conductor design

Application range

Lift cable that ensures the electrical integrity in various areas of lift construction

Suitable for use in outdoor lifts

The application profiles for ÖLFLEX® CRANE and ÖLFLEX® LIFT cables can be found in the appendix, selection table A3

The assembly and handling guidelines for ÖLFLEX® CRANE cables can be found in the catalogue appendix, technical table T4; for ÖLFLEX® LIFT cables please see the catalogue appendix, technical table T5

Product features

Last Update (14.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® LIFT N

Flame-retardant according IEC 60332-1-2
Good weather-resistance

Product Make-up

Conductor made of bare copper wires
Special PVC-based core insulation
Supporting element made of synthetic fibre
Fleece-wrapping between cores and sheath
Special PVC-based outer sheath

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000826 ETIM 5.0/6.0 Class-Description: Coding for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000826 ETIM 6.0 Class-Description: Elevator cable
Core identification code:	Black with white numbers acc. to VDE 0293-334
Suspension length:	refer to article table
Conductor stranding:	Extra-fine wire according to VDE 0295, class 6/IEC 60228 class 6
Minimum bending radius:	Flexible use: 20 x outer diameter
Nominal voltage:	U0/U: 300/500 V
Test voltage:	4000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Flexible use: -15°C to +70°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil \leq 30 kg or \leq 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® LIFT N

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Max. suspension length (m)	Copper index (kg/km)	Weight (kg/km)
2027019	5 G 1.0	9.8	50	48	129
2027020	7 G 1.0	11.3	80	67.2	190
2027022	12 G 1.0	16.1	80	115.2	370
2027024	18 G 1.0	16.3	60	172.8	430
2027027	24 G 1.0	19.3	60	230.4	595
2027029	36 G 1.0	22	90	345.6	815

Last Update (14.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16