

N2XS(F)2Y

Longitudinally water-tight PE medium voltage cable with copper conductor

N2XS(F)2Y, VDE, PE medium voltage cable acc. VDE 0276-620, with copper conductor, longitudinally water-tight, for fixed installation

Info

3 voltage classes: 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV
With copper conductor



Suitable for outdoor use



Mechanical resistance



UV-resistant



Waterproof

Application range

Power and control cable for fixed installation in the following applications:

In water, in ground, outdoors and indoors

In cable trays for power stations, industry, and distribution networks

Also suitable for applications where longitudinal water propagation inside the cable should be avoided.

Burial without additional, suitable underground protection according to HD 620/VDE 0276-620 - Part 10-C (point 4): normal minimum installation depth 0.6 m, but at least 0.8 m under roads

Product features

Suitable for installation or operation under high mechanical stress due to the PE-sheath

Current rating according to HD 620/VDE 0276-620, Part 10-C, Table 7 (buried at +20 °C ground temperature according to HD 620/VDE 0276-620, Part 10-C, point 5) for routing underground and Table 8 (in the air at an air temperature of +30 °C according to HD 620/VDE 0276-620, Part 10-C, point 5) when used outdoors; but always taking into consideration corrections/reductions to the

Last Update (09.08.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

N2XS(F)2Y

current rating that may be necessary according to VDE 0298-4, and VDE 0298-4 (also refer to the catalogue appendix T12) for installation in and on buildings

Norm references / Approvals

HD 620/ VDE 0276-620

Product Make-up

Copper conductor

Abbreviation "rm":

r = round conductor form;

m = multi-wire conductor

Core insulation: Cross-linked Polyethylen (XLPE)

Screen made of copper wires with one or two copper bond counter spiral longitudinally water-tight wrapping

Outer sheath: PE, black

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001140 ETIM 5.0 Class-Description: Medium voltage power cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001140 ETIM 6.0 Class-Description: Medium voltage power cable
Conductor stranding:	Multi-wire
Minimum bending radius:	Fixed installation: 15 x outer diameter
Nominal voltage:	U_0/U : 6/10 (12) kV, 12/20 (24) kV, 18/30 (36) kV
Test voltage:	Depending on nominal voltage: 6/10 kV: 15 kV 12/20 kV: 30 kV 18/30 kV: 45 kV
Temperature range:	During installation: -40 °C to +70 °C Fixed installation: -40 °C to +90 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Aluminium price basis: excludes aluminium. Refer to catalogue appendix T17 for the application and definition of "Metal price basis" and "Metal index".

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

* Trade product, no Lapp product

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

N2XS(F)2Y

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
6/10 (12) kV				
38107811	1x35 RM/16	24	518	770
38107812	1x50 RM/16	25	662	900
38106992	1X70 RM/16	26	854	1124
3029947	1X95 RM/16	28	1094	1385
38105277	1X120 RM/16	30	1334	1624
1552073	1X150 RM/25	31	1723	1967
38103192	1X185 RM/25	33	2059	2336
30013473	1X240 RM/25	35	2587	2886
38107813	1x300 RM/25	37	3163	3481
38107814	1x400 RM/35	40	4234	4383
38107815	1x500 RM/35	43	5194	5384
38107816	1x630 RM/35	47	6442	6738
12/20 (24) kV				
38801817	1X35 RM/16	28	518	914
38107817	1x50 RM/16	29	662	1050
32700792	1X70 RM/16	31	854	1290
30013472	1X95 RM/16	32	1094	1555
38802324	1X120 RM/16	34	1334	1803
1552043	1X150 RM/25	35	1723	2155
38107818	1x185 RM/25	37	2059	2534
32703444	1X240 RM/25	39	2587	3098
38107819	1x300 RM/25	41	3163	3707
38107820	1x400 RM/35	44	4234	4610
1552048	1X500 RM/35	47	5194	5649
1552042	1X630 RM/35	51	6442	7051
18/30 (36) kV				
38107821	1x50 RM/16	34	662	1261
38107822	1x70 RM/16	36	854	1507
38107823	1x95 RM/16	37	1094	1790
38107824	1x120 RM/16	39	1334	2050
1552044	1X150 RM/25	40	1723	2411
1550992	1X185 RM/25	42	2059	2803
38106652	1X240 RM/25	44	2587	3384

Last Update (09.08.2022)

©2022 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16

N2XS(F)2Y

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
38107825	1x300 RM/25	46	3163	4011
38107826	1x400 RM/35	49	4234	4937
38104163	1X500 RM/35	53	5194	6012
38107827	1x630 RM/35	56	6442	7425
38107828	1x800 RM/35	61	8074	9226

Last Update (09.08.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16