

ÖLFLEX® HEAT 180 GLS

Steel-armoured silicone cables for increased mechanical stress

ÖLFLEX® HEAT 180 GLS - steel-armoured silicone power and control cable for use in machines, plant construction and toolbuilding for temperatures up to +180°C

Info

Protected against thermal and mechanical loads



Halogen-free



Cold-resistant



Mechanical resistance



Temperature-resistant

Benefits

Close-meshed braid made of galvanised steel wires protects against mechanical damage

Longer durability in harsh applications than conventional silicone cables

Possesses insulating properties after combustion due to remaining SiO₂ ash on the conductor

Application range

Areas with high ambient temperatures and occasionally mechanical stress

Typical fields of application

- Steel and glass works
- Cement and ceramic works
- Foundries
- Shipbuilding industry
- Furnace construction

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® HEAT 180 GLS

Product features

Halogen-free (IEC 60754-1), no corrosive gases (IEC 60754-2), flame-retardant (IEC 60332-1-2)

Only suitable for use in dry conditions

Adequate ventilation must be ensured, since the mechanical properties of silicone cables decrease from +100°C in the absence of air

Product Make-up

Fine-wire, tinned-copper conductor

Silicone-based core insulation

Cores twisted together

Silicone-based outer sheath,

colour red-brown

Glass fibre wrapping

Galvanised steel wire braiding

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class-Description: Flexible cable
Core identification code:	Colours according to VDE 0293-308, refer to Appendix T9 From 6 cores: black with white numbers
Conductor stranding:	Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5
Minimum bending radius:	Occasional flexing: 20 x outer diameter Fixed installation: 4 x outer diameter
Nominal voltage:	U ₀ /U: 300/500 V
Test voltage:	2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	-50 °C to +180 °C (adequate ventilation required)

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® HEAT 180 GLS

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® HEAT 180 GLS				
0046201	2 X 0.75	7.6	14.4	84
0046202	3 G 0.75	8	21.6	96
00462033	4 G 0.75	8.8	28.8	118
00462043	5 G 0.75	9.7	36	145
0046205	6 G 0.75	10.4	43.2	167
0046206	7 G 0.75	10.4	50.4	171
0046207	2 X 1.0	7.8	19.2	92
0046208	3 G 1.0	8.2	28.8	106
00462093	4 G 1.0	9.1	38.4	132
00462103	5 G 1.0	10	48	161
0046212	7 G 1.0	10.7	67	205
0046213	2 X 1.5	8.8	29	119
0046214	3 G 1.5	9.2	43	140
00462153	4 G 1.5	10	57.6	168
00462163	5 G 1.5	10.8	72	212
0046218	7 G 1.5	11.8	101	255
0046237	12 G 1.5	15.4	173	433
0046219	2 X 2.5	10	48	162
0046220	3 G 2.5	10.9	72	217
00462213	4 G 2.5	12	96	260
00462223	5 G 2.5	13	120	310
0046224	7 G 2.5	14	168	362
0046226	3 G 4.0	12.9	115	300
00462273	4 G 4.0	14	154	365
00462283	5 G 4.0	15.4	192	446
00462313	4 G 6.0	16.1	230	500
00462343	4 G 10.0	20.8	384	807
00462353	4 G 16.0	22.8	614	1117

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16