


## ÖLFLEX® SERVO Core Line for Siemens 6FX5002 (PVC)

Core Line for light duty power chain applications

### Info

Connector with novel, safe screen connection

Custom length available



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Optimum strain relief



Robust



Reliability



Connector with standard housing unit



Waterproof

### Benefits

Regional manufactured worldwide available

Lapp quality standards

Last Update (15.02.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## ÖLFLEX® SERVO Core Line for Siemens 6FX5002 (PVC)

### Application range

Food production and packaging machinery  
Woodworking Machinery  
For travel distances up to 10 m  
For static and dynamic applications  
Chain application

### Product features

Core Line for light duty power chain applications  
New PVC servo cable, shielded  
Innovative connector concept

### Norm references / Approvals

Design according to SIEMENS® standard

### Product Make-up

Brake wire with 1.5 mm<sup>2</sup> wire gauge

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Core identification code:	Supply cores: colored with white printing Brown with white printing: V / L2 Black with white printing: U/L1/C/L + Gray with white printing: W/L3/D/L-GN/GE protective conductor/control wires: WS; SW
Conductor stranding:	Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5
Minimum bending radius:	Chain application: 7,5 x cable diameter Fixed installation: 4 x cable diameter
Nominal voltage:	Power cores and control cores: IEC U0/U: 600/1000 V UL & CSA: 1000 V
Test voltage:	Core/Core: 4 kV Core/Screen: 4 kV
Protective conductor:	G = with GN-YE protective conductor
Temperature range:	Chain application: -5°C to +70°C (UL: +80°C) Fixed installation: -40°C to +80°C
Alternating bending cycles:	5 mio. cycles

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.  
Siemens part designations (6FX5002/5008, 6FX7002/7008, 6FX8002/8008) are registered trademarks of Siemens AG, and are listed for comparison purposes only  
Other lengths and cable terminations are available upon request.  
Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.  
Further Article and length online <https://servoconfigurator.lappgroup.com/>

**ÖLFLEX® SERVO Core Line for Siemens 6FX5002 (PVC)**

Article number	Outer dimensions (mm)	Length (m)	Number of cores and mm <sup>2</sup> per conductor	SIEMENS® assembly designation	Copper index kg/1.000 pieces	Other dimensions	PU
ÖLFLEX® SERVO Core Line for Siemens 6FX5002 (PVC)							
5480007020	9.4	10.0	4 G 1,5	5CA05	818.1	Other lengths available	1
5480007090	11.1	10.0	4 G 2,5	5CA15	1212	Other lengths available	1
5480007510	9.4	10.0	4 G 1,5	5CN01	830.25	Other lengths available	1
5480007650	11.1	10.0	4 G 2,5	5CN11	1230	Other lengths available	1
5480007720	9.4	10.0	4 G 1,5	5CN21	830.25	Other lengths available	1
5480007790	11.1	10.0	4 G 2,5	5CN31	1230	Other lengths available	1
5480008210	11.1	10.0	4 G 2,5	5CQ15	1212	Other lengths available	1
5480008630	9.4	10.0	4 G 1,5	5CS01	830.25	Other lengths available	1

Last Update (15.02.2020)

©2020 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

 You can find the current technical data in the corresponding data sheet.  
 PN 0456 / 02\_03\_16