

ÖLFLEX® SERVO Core Line for Siemens 6FX5002 (PVC)

Core Line for light duty power chain applications

Info

Connector with novel, safe screen connection Custom length available







Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Optimum strain relief



Robust



Reliability



Connector with standard housing unit



Waterproof

Benefits

Regional manufactured worldwide available Lapp quality standards

Last Update (06.08.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16



ÖLFLEX® SERVO Core Line for Siemens 6FX5002 (PVC)

Application range

Food production and packaging machinery Woodworking Machinery For travel distances up to 10 m For static and dynamic applications Chain application

Product features

Core Line for light duty power chain applications New PVC servo cable, shielded Innovative connector concept

Norm references / Approvals

Design according to SIEMENS® standard

Product Make-up

Brake wire with 1.5 mm² wire gauge

Technical Data

Classification ETIM 5: ETIM 5.0 Class-ID: EC000104

ETIM 5.0 Class-Description: Control cable

Core identification code: Supply cores: colored with white printing

Brown with white printing: V / L2 Black with white printing: U/L1/C/L +

Gray with white printing: W/L3/D/L-GN/GE protective

conductorcontrol wires: WS; SW

Conductor stranding: Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5

Minimum bending radius: Chain application:7,5 x cable diameter

Fixed installation: 4 x cable diameter

Nominal voltage: Power cores and control cores:

IEC U0/U: 600/1000 V UL & CSA: 1000 V

Test voltage: Core/Core: 4 kV

Core/Screen: 4 kV

Protective conductor: G = with GN-YE protective conductor

Temperature range: Chain application:-5°C to +70°C (UL: +80°C)

Fixed installation: -40°C to +80°C

Alternating bending cycles: 5 mio. cycles

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Siemens part designations (6FX5002/5008, 6FX7002/7008, 6FX8002/8008) are registered trademarks of Siemens AG, and are listed for comparison purposes only

Other lengths and cable terminations are available upon request.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Further Article and length online https://servoconfigurator.lappgroup.com/

Last Update (06.08.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16



ÖLFLEX® SERVO Core Line for Siemens 6FX5002 (PVC)

Article number	Outer dimensions (mm)	Length (m)	Number of cores and mm² per conductor	SIEMENS® assembly designation	Copper index kg/1.000 pieces	Other dimensions	PU
ÖLFLEX® SERVO	Core Line for Siemens 6	FX5002 (PVC)		•	•	•	•
5480007020	9.4	10.0	4 G 1,5	5CA05	818.1	Other lengths available	1
5480007090	11.1	10.0	4 G 2,5	5CA15	1212	Other lengths available	1
5480007510	9.4	10.0	4 G 1,5	5CN01	830.25	Other lengths available	1
5480007650	11.1	10.0	4 G 2,5	5CN11	1230	Other lengths available	1
5480007720	9.4	10.0	4 G 1,5	5CN21	830.25	Other lengths available	1
5480007790	11.1	10.0	4 G 2,5	5CN31	1230	Other lengths available	1
5480008210	11.1	10.0	4 G 2,5	5CQ15	1212	Other lengths available	1