

ÖLFLEX® SERVO Extended Line according to Siemens 6FX8002 (PUR)

Core Line for light duty power chain applications









Info

Classical production and assembly

Connector with novel, safe screen connection

For the most demanding mechanical requirements



-  Supplementary automation components from Lapp
-  Mechanical and plant engineering
-  Mechanical resistance
-  Optimum strain relief
-  Robust
-  Reliability
-  Connector with standard housing unit
-  Waterproof

Benefits

Regional manufactured worldwide available

Lapp quality standards

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® SERVO Extended Line according to Siemens 6FX8002 (PUR)

Application range

Specifically for machine tool building
Designed for power chain use: for travel distances up to 100 m (horizontal)
For very high dynamic motion sequences

Product features

Extended Line for high mechanical stress in Power chains
Proven for high dynamic stresses and long distances

Norm references / Approvals

Design according to SIEMENS® standard 6FX 8002
Flame-retardant according to IEC 60332-1-2, VW-1, FT1

Product Make-up

Full range of types
brake wire with 1.5mm² wire gauge

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Core identification code:	Power cores: black with marking U/L1/C/L+; V/L2; W/L3/D /L-; GN/YE protective conductor Optional designs with one pair of control cores: black; white Two pairs of control cores: black with white numbers: 5, 6, 7, 8
Conductor stranding:	Extra-fine wire according to VDE 0295, class 6/IEC 60228 class 6
Minimum bending radius:	For flexible use: 7.5 x outer diameter (1.5-16 mm ²) 10 x outer diameter (25-50 mm ²) Fixed installation: 4 x outer diameter
Nominal voltage:	Power cores and control cores: IEC U0/U: 600/1000 V UL & CSA: 1000 V
Test voltage:	Core/Core: 4 kV Core/Screen: 4 kV
Protective conductor:	G = with GN-YE protective conductor
Temperature range:	Flexing: -40 °C to +90 °C (UL/CSA: +80 °C) Fixed installation: -50 °C to +90 °C (UL/CSA: +80 °C)
Alternating bending cycles:	10 mio. cycles

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.
Siemens part designations (6FX5002/5008, 6FX7002/7008, 6FX8002/8008) are registered trademarks of Siemens AG, and are listed for comparison purposes only
Other lengths and cable terminations are available upon request.

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

**ÖLFLEX® SERVO Extended Line according to Siemens 6FX8002
(PUR)**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
Further Article and length online <https://servoconfigurator.lappgroup.com/>

ÖLFLEX® SERVO Extended Line according to Siemens 6FX8002 (PUR)

Article number	Length (m)	SIEMENS® assembly designation	Copper index kg/1.000 pieces	Other dimensions	PU
ÖLFLEX® SERVO Core Line for Siemens 6FX8002 (PUR)					
5480000015	10.0	2AD00	680	Other lengths available	1
5480000065	10.0	2AH00	790	Other lengths available	1
5480000165	10.0	2CA31	860	Other lengths available	1
5480000290	10.0	2CH00	680	Other lengths available	1
5480000390	10.0	2DC10	380	Other lengths available	1
5480000415	10.0	2DC20	380	Other lengths available	1
5480000440	10.0	2EQ10	860	Other lengths available	1
5480004940	10.0	5CN51	3034	Other lengths available	1
5480005290	10.0	5CS13	4,624.7	Other lengths available	1
5480005440	10.0	5CS51	3034	Other lengths available	1
5480005990	10.0	5DN51	3,372.25	Other lengths available	1

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16