

ÖLFLEX® TRAIN 371 1,8kV

Single-core cable according to EN 50264-3-1 type MM for high requirements in railway applications

ÖLFLEX® TRAIN 371 1,8kV - Single-core cable EN 50264-3-1 type MM, 1,8/3kV for high requirements in railways/rolling stock
EN 45545: HL1-HL3, NF F 16-101: C/F1

Info

Meets EN 50264-3-1 type MM and
EN 45545-2

High temperature resistance: -50°C up to 120°C

Highly oil- and fuel-resistant



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Mechanical resistance



Oil-resistant



Temperature-resistant



UV-resistant

Benefits

Last Update (25.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® TRAIN 371 1,8kV

High electrical strength and mechanical durability due to dual-layer cable construction

Good chemical resistance please see Appendix T1

Resistant to mechanical influences in harsh environmental conditions

Extended temperature range

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

Application range

For use in railway vehicles, for fixed installations and applications where limited movement may occur

Suitable for wiring of control cabinets, distributors, converters, motors and batteries

Also applicable within oily environments and areas with increased ambient temperature

Product features

Fire behaviour according to EN/IEC:

- Halogen-free acc. to EN 60754-1
- No corrosive gases acc. to EN 60754-2
- No fluorine acc. to EN 60684-2
- No toxic gases acc. to EN 50305
- Low smoke density acc. to EN 61034-2
- Flame-retardant acc. to EN 60332-1-2
- No flame propagation acc. to EN 60332-3-24 / EN 60332-3-25 / EN 50305

Fire behaviour according to NF:

- Toxicity of gases acc. to NF X 70-100
- Low smoke density acc. to NF X 10-702
- No flame propagation acc. to NF C 32-070, Cat. C1 and C2

Chemical properties:

- Oil resistant acc. to EN 50264-3-1
- Fuel resistant acc. to EN 50264-3-1
- Acid resistant acc. to EN 50264-3-1
- Alkali resistant acc. to EN 50264-3-1
- Ozone resistant acc. to EN 50264-3-1/ EN 50305)

Current rating according to EN 50355, appendix A

Norm references / Approvals

EN 50382-2 type FF

EN 45545-2 HL1, HL2, HL3

NF F 16-101 - Classification: C / F1
(flame propagation / smoke)

Product Make-up

Tinned-copper strand, fine-wire

Insulation: Electron beam cross-linked Polymer compound EI 109

Outer sheath: electron beam cross-linked polymer-compound EM 104

Outer sheath colour: Black

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000057

ETIM 5.0 Class-Description: Low voltage power cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000057

ETIM 6.0 Class-Description: Low voltage power cable

Last Update (25.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® TRAIN 371 1,8kV

Conductor stranding:	Fine-wired/ Finely stranded according to IEC 60228, conductor class 5
Minimum bending radius:	Fixed installation: ≤ 12 mm: 4 x OD / 3 x OD* > 12 mm: 5 x OD / 4 x OD* * for careful bending, once at connecting terminal
Nominal voltage:	U ₀ /U AC 1.8/3 kV U _m AC 3,6 kV V ₀ DC 2,7 kV
Test voltage:	6,5 kV AC; 15 kV DC
Temperature range:	-40 °C to +120 °C (20.000 h) -50 °C acc. to GOST 20.57.406-81

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® TRAIN 371 1,8kV

Article number	Conductor cross-section (mm ²)	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
15371000	1.5	5.8	14.4	56.3
15371001	2.5	6.2	24	66.7
15371002	4.0	6.9	38.4	89.7
15371003	6.0	7.4	57.6	115.6
15371004	10.0	8.8	96	173.3
15371005	16.0	9.8	153.6	243.6
15371006	25.0	12.1	240	374.3
15371007	35.0	13.3	336	487.7
15371008	50.0	15.3	480	659.4
15371009	70.0	17.0	672	875.3
15371010	95.0	19.8	912	1,180.3
15371011	120.0	21.4	1152	1,440.6
15371012	150.0	23.8	1440	1,787.7
15371013	185.0	25.7	1776	2,166.2
15371014	240.0	29.2	2304	2,774.8
15371015	300.0	30.4	2880	3,366.8

Last Update (25.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16