

ÖLFLEX® SERVO 728 CY

Screened encoder cable with PVC outer sheath for static use - certified

ÖLFLEX® SERVO 728 CY - shielded rotary encoder cable for fixed installation or occasional flexing with UL/cUL AWM certification

Info

Successor of ÖLFLEX® SERVO 720 CY
 Fits to various encoder systems
 Low-capacitance design



Oil-resistant



Interference signals

Benefits

Suitable for use with encoders & resolvers from leading manufacturers
 Thin, optimised for weight and volume
 Multi-standard certification reduces part varieties and saves costs
 Easy to install

Application range

Analogue and incremental encoders in servo drives
 For static and occasionally flexible use
 Measurement, control and electrical applications
 Industrial machinery and plant engineering
 Only for outdoor use within the indicated operating temperature range, with UV-protection

Product features

Flammability:
 UL/CSA: VW-1, FT1
 IEC/EN: 60332-1-2

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® SERVO 728 CY

Low attenuation ensures a longer transmission distance
Oil-resistant

Norm references / Approvals

UL AWM Style 2464
cUL AWM I/II A/B FT1
UL File No. E63634

Product Make-up

Fine-wire, tinned-copper conductor
Core insulation: polypropylene (PP)
Cores (or core pairs) twisted in layers or bundles
Refer to data sheet for more details
Non-woven wrapping
PVC jacket, green (RAL 6018)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Core identification code:	Details see datasheet ÖLFLEX® SERVO 728 CY
Conductor stranding:	Fine wire acc. to VDE 0295, class 5 / IEC 60228 class 5 from 0.5 mm ²
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 6 x outer diameter
Nominal voltage:	IEC: 30 V UL & CSA: 300 V
Test voltage:	C/C: 2000 V C/S: 1000 V
Temperature range:	Occasional flexing: -5 °C to +70 °C (UL: +80 °C) Fixed installation: -40 °C to +80 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® SERVO 728 CY

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1020100	(10x0,14+2x0,5)	7.0	41	84
1020101	(10x0,14+4x0,5)	7.6	53	101
1020102	(15x0,14+4x0,5)	7.6	68	115
1020133	(4x2x0,14+4x0,5)	7.9	58	97
1020134	(7x2x0,14+2x0,5)	8.5	60	115
1020110	(4x2x0,34+4x0,5)	8.3	79	129
1020111	(3x(2x0,14)+4x0,14+2x0,5)	8.2	68	120
1020135	(3x(2x0,14)+ 4x0,14+2x0,5+4x0,22)	9.7	80	160
1020120	(4x2x0,25+2x0,5)	7.9	59	103
1020121	(4x2x0,25+2x1,0)	7.6	63	112
1020122	(4x2x0,14+4x1,0+(4x0,14))	9.0	110	155
1020130	(3x(2x0,14)+2x(0,5))	9.0	87	140
1020136	3x(2x0,14)+(2x0,5)	9.3	87	140
1020131	3x(2x0,14)+(3x0,14)	9.2	41	115
1020132	4x(2x0,14)+(2x1,0)	10.4	84	145
1020140	(5x2x0,25)	7.4	50	96
1020141	(6x2x0,25)	8.0	60	114
1020142	(5x2x22AWG)	7.9	71	115

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16