

ÖLFLEX® TRAIN 361 1,8kV

Single-core cable according to EN 50264-3-1 type M for high requirements in railway applications

ÖLFLEX® TRAIN 361 1,8kV - Single-core EN 50264-3-1 type M, 1,8/3kV for high requirements in railways/rolling stock
EN 45545: HL1-HL3, NF F 16-101: C/F1

Info

Meets EN 50264-3-1 type M and
EN 45545-2

High temperature resistance: -50°C up to 120°C

Highly oil- and fuel-resistant



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Mechanical resistance



Oil-resistant



Temperature-resistant



UV-resistant

Benefits

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® TRAIN 361 1,8kV

Good chemical resistance please see Appendix T1

Resistant to mechanical influences in harsh environmental conditions

Extended temperature range

Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

Application range

For use in railway vehicles, for fixed installations and applications where limited movement may occur

Suitable for connecting lamps, heating equipment, switchgear, terminal boxes and power supply

Also applicable within oily environments and areas with increased ambient temperature

Product features

Fire behaviour according to EN/IEC:

- Halogen-free acc. to EN 60754-1
- No corrosive gases acc. to EN 60754-2
- No fluorine acc. to EN 60684-2
- No toxic gases acc. to EN 50305
- Low smoke density acc. to EN 61034-2
- Flame-retardant acc. to EN 60332-1-2
- No flame propagation acc. to EN 60332-3-24 / EN 60332-3-25 / EN 50305

Fire behaviour according to NF:

- Toxicity of gases acc. to NF X 70-100
- Low smoke density acc. to NF X 10-702
- No flame propagation acc. to NF C 32-070, Cat. C1 and C2

Chemical properties:

- Oil resistant acc. to EN 50264-3-1
- Fuel resistant acc. to EN 50264-3-1
- Acid resistant acc. to EN 50264-3-1
- Alkali resistant acc. to EN 50264-3-1
- Ozone resistant acc. to EN 50264-3-1/ EN 50305)

Current rating according to EN 50355, appendix A

Norm references / Approvals

EN 50264-3-1 type M

EN 45545-2 HL1, HL2, HL3

NF F 16-101 - Classification: C / F1

(flame propagation / smoke)

Product Make-up

Tinned-copper strand, fine-wire

Insulation: Electron beam cross-linked Polymer compound EI 109

Colour: Black

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000993

ETIM 5.0 Class-Description: Single core cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000993

ETIM 6.0 Class-Description: Single core cable

Conductor stranding:

Fine-wired/ Finely stranded according to IEC 60228, conductor

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® TRAIN 361 1,8kV

| | |
|-------------------------|---|
| Minimum bending radius: | class 5 Fixed installation: ≤ 12 mm: 3 x OD > 12 mm: 4 x OD Occasional flexing: ≤ 12 mm: 4 x OD > 12 mm ≤ 20 mm: 5 x OD > 20 mm: 6 x OD (OD = outer diameter) |
| Nominal voltage: | U ₀ /U AC 1.8/3 kV U _m AC 3,6 kV V ₀ DC 2,7 kV |
| Test voltage: | 6,5 kV AC; 15 kV DC |
| Temperature range: | Fixed installation: -45°C to +120°C (20.000 h) -50°C acc. to GOST 20.57.406-81 Occasional flexing: -35°C to +90°C Short circuit: +200°C (5s) |

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® TRAIN 361 1,8kV

| Article number | Conductor cross-section (mm ²) | Outer diameter [mm] | Copper index (kg/km) | Weight (kg/km) |
|----------------|--|---------------------|----------------------|----------------|
| 15361000 | 1.5 | 5.6 | 14.4 | 47.5 |
| 15361001 | 2.5 | 6.0 | 24 | 61.3 |
| 15361002 | 4.0 | 6.7 | 38.4 | 80.4 |
| 15361003 | 6.0 | 7.2 | 57.6 | 105 |
| 15361004 | 10.0 | 8.2 | 96 | 152.6 |
| 15361005 | 16.0 | 9.2 | 153.6 | 224 |
| 15361006 | 25.0 | 10.5 | 240 | 322.7 |
| 15361007 | 35.0 | 11.7 | 336 | 431 |
| 15361008 | 50.0 | 13.7 | 480 | 592.2 |
| 15361009 | 70.0 | 15.4 | 672 | 801.4 |
| 15361010 | 95.0 | 17.8 | 912 | 1,075.5 |
| 15361011 | 120.0 | 19.4 | 1152 | 1,328.9 |
| 15361012 | 150.0 | 21.4 | 1440 | 1634 |
| 15361013 | 185.0 | 23.3 | 1776 | 2,011.4 |
| 15361014 | 240.0 | 26.8 | 2304 | 2,570.5 |
| 15361015 | 300.0 | 28.0 | 2880 | 3,175.6 |

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16