

## ÖLFLEX® TRAIN 361 1,8kV

Single-core cable according to EN 50264-3-1 type M for high requirements in railway applications

ÖLFLEX® TRAIN 361 1,8kV - Single-core EN 50264-3-1 type M, 1,8/3kV for high requirements in railways/rolling stock  
EN 45545: HL1-HL3, NF F 16-101: C/F1

### Info

Meets EN 50264-3-1 type M and  
EN 45545-2

High temperature resistance: -50°C up to 120°C

Highly oil- and fuel-resistant



Rail



Good chemical resistance



Flame-retardant



Halogen-free



Cold-resistant



Mechanical resistance



Oil-resistant



Temperature-resistant



UV-resistant

### Benefits

Last Update (20.12.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## ÖLFLEX® TRAIN 361 1,8kV

Good chemical resistance  
Resistant to mechanical influences in harsh environmental conditions  
Extended temperature range  
Reduced flame spreading increases the protection against damage to persons and property in the event of a fire

### Application range

For use in railway vehicles, for fixed installations and applications where limited movement may occur  
Suitable for connecting lamps, heating equipment, switchgear, terminal boxes and power supply  
Also applicable within oily environments and areas with increased ambient temperature

### Product features

Fire behaviour according to EN/IEC:

- Halogen-free acc. to EN 60754-1
- No corrosive gases acc. to EN 60754-2
- No fluorine acc. to EN 60684-2
- No toxic gases acc. to EN 50305
- Low smoke density acc. to EN 61034-2
- Flame-retardant acc. to EN 60332-1-2
- No flame propagation acc. to EN 60332-3-24 / EN 60332-3-25 / EN 50305

Fire behaviour according to NF:

- Toxicity of gases acc. to NF X 70-100
- Low smoke density acc. to NF X 10-702
- No flame propagation acc. to NF C 32-070, Cat. C1 and C2

Chemical properties:

- Oil resistant acc. to EN 50264-3-1
- Fuel resistant acc. to EN 50264-3-1
- Acid resistant acc. to EN 50264-3-1
- Alkali resistant acc. to EN 50264-3-1
- Ozone resistant acc. to EN 50264-3-1/ EN 50305)

Current rating according to EN 50355, appendix A

### Norm references / Approvals

EN 50264-3-1 type M  
EN 45545-2 HL1, HL2, HL3  
NF F 16-101 - Classification: C / F1  
(flame propagation / smoke)

### Product Make-up

Tinned-copper strand, fine-wire  
Insulation: Electron beam cross-linked Polymer compound EI 109  
Colour: Black

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000993 ETIM 5.0 Class-Description: Single core cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000993 ETIM 6.0 Class-Description: Single core cable
Conductor stranding:	Fine-wired/ Finely stranded according to IEC 60228, conductor

Last Update (20.12.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**ÖLFLEX® TRAIN 361 1,8kV**

	class 5
Minimum bending radius:	Fixed installation: ≤ 12 mm: 3 x OD > 12 mm: 4 x OD Occasional flexing: ≤ 12 mm: 4 x OD > 12 mm ≤ 20 mm: 5 x OD > 20 mm: 6 x OD (OD = outer diameter)
Nominal voltage:	U <sub>0</sub> /U AC 1.8/3 kV U <sub>m</sub> AC 3,6 kV V <sub>0</sub> DC 2,7 kV
Test voltage:	6,5 kV AC; 15 kV DC
Temperature range:	Fixed installation: -45°C to +120°C (20.000 h) -50°C acc. to GOST 20.57.406-81 Occasional flexing: -35°C to +90°C Short circuit: +200°C (5s)

**Note**

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® TRAIN 361 1,8kV**

Article number	Conductor cross-section (mm <sup>2</sup> )	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
15361000	1.5	5.6	14.4	47.5
15361001	2.5	6.0	24	61.3
15361002	4.0	6.7	38.4	80.4
15361003	6.0	7.2	57.6	105
15361004	10.0	8.2	96	152.6
15361005	16.0	9.2	153.6	224
15361006	25.0	10.5	240	322.7
15361007	35.0	11.7	336	431
15361008	50.0	13.7	480	592.2
15361009	70.0	15.4	672	801.4
15361010	95.0	17.8	912	1,075.5
15361011	120.0	19.4	1152	1,328.9
15361012	150.0	21.4	1440	1634
15361013	185.0	23.3	1776	2,011.4
15361014	240.0	26.8	2304	2,570.5
15361015	300.0	28.0	2880	3,175.6

Last Update (20.12.2019)

©2019 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16