

Extension- and compensating cables, paired

PVC, silicone, FEP or glass fibre-insulated

Extension and compensating cables, single-paired version - suitable for use in temperature measurement and manufacturing process control

Info

Available in many different designs

New: thermocouple cable type K



Norm references / Approvals

Space-saving and flexible

For more detailed information, see appendix T8 and data sheets

Application range

Allows temperature measurement even in places where non-contact temperature measurement is not possible or reasonable
The thermocouple is used to measure temperature as a part of monitoring the manufacturing process, thus the sheath material should be selected with reference to the maximum ambient temperature at its junction.

Conductor materials (alloys):

Fe/CuNi (LX, JX)

Conductor alloys are identical to thermocouple alloys

NiCr/Ni (K, KX, KCA)

K and KX version - conductor alloys are identical to thermocouple alloys

KCA version: compensating alloys (for KCA: Fe/CuNi), not identical to thermocouple alloys

PtRh/Pt (RCB, SCB)

Compensating alloys (for RCB, SCB: Cu/CuNi) are not identical to thermocouple alloys

Norm references / Approvals

Colour identity code

DIN 43710

Negative conductor and outer sheath:

Fe/CuNi: blue

NiCr/Ni: green

PtRh/Pt: white

Positive conductor: always red

IEC 60 584

Positive conductor and outer sheath:

Fe/CuNi: black

NiCr/Ni: green

PtRh/Pt: orange

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Extension- and compensating cables, paired

Negative conductor: always white

Product Make-up

Design abbreviations:

PVC: Polyvinylchloride

SIL: Silicone rubber

GL: Glass fibre

FEP: Fluorinated ethylene propylene

EGL: E-Glass fibre

C: Copper braiding screen

ST: Aluminium foil screen

S: Steel wire braiding

Design, for example PVC-PVC-S-PVC:

- PVC core insulation

- PVC inner sheath

- Steel wire braiding

- PVC outer sheath

Examples shown (top to bottom):

Fe/CuNi DIN 2 x 1.5 PVC

NiCr/Ni IEC 2 x 1.5 GL-GL

PtRh/Pt IEC 2 x 1.5 GL-GL-S

NiCr/Ni DIN 2 x 1.5 SIL-GL

NiCr/Ni DIN 2 x 1.5 PVC-PVC

PtRh/Pt DIN 2 x 1.5 SIL-SIL

Fe/CuNi IEC 2 x 1.5 SIL-SIL-S

NiCr/Ni IEC 2 x 1.5 SIL

PtRh/Pt IEC 2 x 1.5 SIL-GL-S

Fe/CuNi IEC 2 x 0.22 PVC-PVC-C-PVC

NiCr/Ni IEC 2 x 1.5 PVC-ST-PVC

Fe/CuNi DIN 2 x 1.5 PVC-PVC-S-PVC

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000838

ETIM 5.0 Class-Description: Thermocouple cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000838

ETIM 6.0 Class-Description: Thermocouple cable

Based on:

Limiting deviation in accordance with DIN and IEC in accordance with class 2

Conductor stranding:

1.5 mm²: approx. 48 x 0.20 mm

0.75 mm²: approx. 24 x 0.20 mm

0.5 mm²: approx. 16 x 0.20 mm

0.22 mm²: approx. 7 x 0.20 mm

Minimum bending radius:

Without metal braiding:

12 x cable diameter

With metal braiding:

15 x cable diameter

Temperature range:

(referring to insulation and sheath material)

PVC: -5°C to +80°C

Silicone: -25°C to +180°C

Glass fibre: -25°C to +200°C

FEP: -100°C to +205°C

E-Glass: -25°C to +400°C

Extension- and compensating cables, paired

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil \leq 30 kg or \leq 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Extension- and compensating cables, paired

Article number	Reference/article designation	Thermocouple	Product Make-up	Cable design	Number of cores and mm ² per conductor	Outer diameter [mm]	Outer dimensions, width x height (mm)	Weight (kg/km)
0.22 mm ² extension and compensating cables								
0151051	KE 9-022 L	Fe/CuNi	DIN LX	PVC-PVC	2 x 0.22	4	-	22
0161051	KE 9-022 L	Fe/CuNi	IEC JX	PVC-PVC	2 x 0.22	4	-	22
0152051	KN 9-022 L	NiCr/Ni	DIN KCA	PVC-PVC	2 x 0.22	4	-	22
0162051	KN 9-022 L	NiCr/Ni	IEC KCA	PVC-PVC	2 x 0.22	4	-	22
0153051	KP 9-022 L	PtRh/Pt	DIN RCB, SCB	PVC-PVC	2 x 0.22	4	-	22
0163051	KP 9-022 L	PtRh/Pt	IEC RCB, SCB	PVC-PVC	2 x 0.22	4	-	22
0151052	KE 5-022 L-CY	Fe/CuNi	DIN LX	PVC-PVC-C-PVC	2 x 0.22	4.9	-	31
0161052	KE 5-022 L-CY	Fe/CuNi	IEC JX	PVC-PVC-C-PVC	2 x 0.22	4.9	-	31
0152052	KN 5-022 L-CY	NiCr/Ni	DIN KCA	PVC-PVC-C-PVC	2 x 0.22	4.9	-	31
0162052	KN 5-022 L-CY	NiCr/Ni	IEC KCA	PVC-PVC-C-PVC	2 x 0.22	4.9	-	31
0153052	KP 5-022 L-CY	PtRh/Pt	DIN RCB, SCB	PVC-PVC-C-PVC	2 x 0.22	4.9	-	31
0163052	KP 5-022 L-CY	PtRh/Pt	IEC RCB, SCB	PVC-PVC-C-PVC	2 x 0.22	4.9	-	31
1161011	KN FEP-SIL	NiCr/Ni	IEC KCA	FEP-SIL	2 x 0.22	3.8	-	22
1161007	K FEP-C-FEP	NiCr/Ni	IEC K	FEP-C-FEP	2 x 0.22	3	-	22
Thermocouple cable type K, 0,5 mm								
1161008	K FEP-FEP	NiCr/Ni	IEC K	FEP-FEP ovale	2 x 0.5	-	2.4 x 1.5	45
1161009	K GL-GL	NiCr/Ni	IEC K	EGL-EGL ovale	2 x 0.5	-	2.3 x 1.3	45
0.5 mm ² extension and compensating cables								
0151030	KE 91 L	Fe/CuNi	DIN LX	PVC-PVC	2 x 0.5	5.4	-	45
0161030	KE 91 L	Fe/CuNi	IEC JX	PVC-PVC	2 x 0.5	5.4	-	45
0152040	KN 91 L	NiCr/Ni	DIN KCA	PVC-PVC	2 x 0.5	5.4	-	45
0162040	KN 91 L	NiCr/Ni	IEC KCA	PVC-PVC	2 x 0.5	5.4	-	45
0151040	KE 41 L-SIL	Fe/CuNi	DIN LX	SIL-SIL-S ovale	2 x 0.5	-	6.4 x 4.4	51
0161040	KE 41 L-SIL	Fe/CuNi	IEC JX	SIL-SIL-S ovale	2 x 0.5	-	6.4 x 4.4	51
0152030	KN 41 L-SIL	NiCr/Ni	DIN KCA	SIL-SIL-S ovale	2 x 0.5	-	6.4 x 4.4	51
0162030	KN 41 L-SIL	NiCr/Ni	IEC KCA	SIL-SIL-S ovale	2 x 0.5	-	6.4 x 4.4	51
0.75 mm ² extension and compensating cables								
0151035	KE 92 L	Fe/CuNi	DIN LX	PVC-PVC	2 x 0.75	6	-	56
0161035	KE 92 L	Fe/CuNi	IEC JX	PVC-PVC	2 x 0.75	6	-	56
0152045	KN 92 L	NiCr/Ni	DIN KCA	PVC-PVC	2 x 0.75	6	-	56
0162045	KN 92 L	NiCr/Ni	IEC KCA	PVC-PVC	2 x 0.75	6	-	56
0151050	KE 42 L-SIL	Fe/CuNi	DIN LX	SIL-SIL-S ovale	2 x 0.75	-	6.4 x 4.4	58
0161050	KE 42 L-SIL	Fe/CuNi	IEC JX	SIL-SIL-S ovale	2 x 0.75	-	6.4 x 4.4	58

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03.16

Extension- and compensating cables, paired

Article number	Reference/article designation	Thermocouple	Product Make-up	Cable design	Number of cores and mm ² per conductor	Outer diameter [mm]	Outer dimensions, width x height (mm)	Weight (kg/km)
0152035	KN 42 L-SIL	NiCr/Ni	DIN KCA	SIL-SIL-S ovale	2 x 0.75	-	6.4 x 4.4	58
0162035	KN 42 L-SIL	NiCr/Ni	IEC KCA	SIL-SIL-S ovale	2 x 0.75	-	6.4 x 4.4	58
PVC-insulated versions 1,5 mm ²								
0151001	KE 1 L	Fe/CuNi	DIN LX	PVC	2 x 1.5	5.4	-	40
0161001	KE 1 L	Fe/CuNi	IEC JX	PVC	2 x 1.5	5.4	-	40
0152001	KN 1 L	NiCr/Ni	DIN KCA	PVC	2 x 1.5	5.4	-	40
0162001	KN 1 L	NiCr/Ni	IEC KCA	PVC	2 x 1.5	5.4	-	40
0151010	KE 9 L	Fe/CuNi	DIN LX	PVC-PVC round	2 x 1.5	7.1	-	79
0161010	KE 9 L	Fe/CuNi	IEC JX	PVC-PVC round	2 x 1.5	7.1	-	79
0152010	KN 9 L	NiCr/Ni	DIN KCA	PVC-PVC round	2 x 1.5	7.1	-	79
0162010	KN 9 L	NiCr/Ni	IEC KCA	PVC-PVC round	2 x 1.5	7.1	-	79
0154010	KXN 9 L	NiCr/Ni	DIN KX	PVC-PVC round	2 x 1.5	7.1	-	79
0164010	KXN 9 L	NiCr/Ni	IEC KX	PVC-PVC round	2 x 1.5	7.1	-	79
0153010	KP 9 L	PtRh/Pt	DIN RCB, SCB	PVC-PVC round	2 x 1.5	7.1	-	79
0163010	KP 9 L	PtRh/Pt	IEC RCB, SCB	PVC-PVC round	2 x 1.5	7.1	-	79
0151017	KE 12 L	Fe/CuNi	DIN LX	PVC-PVC ovale	2 x 1.5	-	7.2 x 4.4	69
0161017	KE 12 L	Fe/CuNi	IEC JX	PVC-PVC ovale	2 x 1.5	-	7.2 x 4.4	69
0152017	KN 12 L	NiCr/Ni	DIN KCA	PVC-PVC ovale	2 x 1.5	-	7.2 x 4.4	69
0162017	KN 12 L	NiCr/Ni	IEC KCA	PVC-PVC ovale	2 x 1.5	-	7.2 x 4.4	69
0154011	KE 20 L	Fe/CuNi	DIN LX	PVC-ST-PVC	2 x 1.5	7.6	-	85
0164011	KE 20 L	Fe/CuNi	IEC JX	PVC-ST-PVC	2 x 1.5	7.6	-	85
0154012	KN 20 L	NiCr/Ni	DIN KCA	PVC-ST-PVC	2 x 1.5	7.6	-	85
0164012	KN 20 L	NiCr/Ni	IEC KCA	PVC-ST-PVC	2 x 1.5	7.6	-	85
0154013	KXN 20 L	NiCr/Ni	DIN KX	PVC-ST-PVC	2 x 1.5	7.6	-	85
0164013	KXN 20 L	NiCr/Ni	IEC KX	PVC-ST-PVC	2 x 1.5	7.6	-	85
0154014	KP 20 L	PtRh/Pt	DIN RCB, SCB	PVC-ST-PVC	2 x 1.5	7.6	-	85
0164014	KP 20 L	PtRh/Pt	IEC RCB, SCB	PVC-ST-PVC	2 x 1.5	7.6	-	85
0151011	KE 9 L-S	Fe/CuNi	DIN LX	PVC-PVC-S	2 x 1.5	8	-	140
0161011	KE 9 L-S	Fe/CuNi	IEC JX	PVC-PVC-S	2 x 1.5	8	-	140
0152011	KN 9 L-S	NiCr/Ni	DIN KCA	PVC-PVC-S	2 x 1.5	8	-	140
0162011	KN 9 L-S	NiCr/Ni	IEC KCA	PVC-PVC-S	2 x 1.5	8	-	140
0157514	KE 9 L-SY	Fe/CuNi	DIN LX	PVC-PVC-S-PVC	2 x 1.5	10.3	-	160
0167514	KE 9 L-SY	Fe/CuNi	IEC JX	PVC-PVC-S-PVC	2 x 1.5	10.3	-	160
0157513	KN 9 L-SY	NiCr/Ni	DIN KCA	PVC-PVC-S-PVC	2 x 1.5	10.3	-	160

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16

Extension- and compensating cables, paired

Article number	Reference/article designation	Thermocouple	Product Make-up	Cable design	Number of cores and mm ² per conductor	Outer diameter [mm]	Outer dimensions, width x height (mm)	Weight (kg/km)
0167513	KN 9 L-SY	NiCr/Ni	IEC KCA	PVC-PVC-S-PVC	2 x 1.5	10.3	-	160
0157515	KP 9 L-SY	PtRh/Pt	DIN RCB, SCB	PVC-PVC-S-PVC	2 x 1.5	10.3	-	160
0167515	KP 9 L-SY	PtRh/Pt	IEC RCB, SCB	PVC-PVC-S-PVC	2 x 1.5	10.3	-	160
Silicone-insulated versions 1.5 mm ²								
0151003	KE 1 L-SIL	Fe/CuNi	DIN LX	SIL	2 x 1.5	5.4	-	40
0161003	KE 1 L-SIL	Fe/CuNi	IEC JX	SIL	2 x 1.5	5.4	-	40
0152003	KN 1 L-SIL	NiCr/Ni	DIN KCA	SIL	2 x 1.5	5.4	-	40
0162003	KN 1 L-SIL	NiCr/Ni	IEC KCA	SIL	2 x 1.5	5.4	-	40
0151022	KE 15 L-SIL	Fe/CuNi	DIN LX	SIL-SIL round	2 x 1.5	7	-	76
0161022	KE 15 L-SIL	Fe/CuNi	IEC JX	SIL-SIL round	2 x 1.5	7	-	76
0152022	KN 15 L-SIL	NiCr/Ni	DIN KCA	SIL-SIL round	2 x 1.5	7	-	76
0162022	KN 15 L-SIL	NiCr/Ni	IEC KCA	SIL-SIL round	2 x 1.5	7	-	76
0153022	KP 15 L-SIL	PtRh/Pt	DIN RCB, SCB	SIL-SIL round	2 x 1.5	7	-	76
0163022	KP 15 L-SIL	PtRh/Pt	IEC RCB, SCB	SIL-SIL round	2 x 1.5	7	-	76
0151023	KE 15 L-SIL-S	Fe/CuNi	DIN LX	SIL-SIL-S round	2 x 1.5	7.8	-	105
0161023	KE 15 L-SIL-S	Fe/CuNi	IEC JX	SIL-SIL-S round	2 x 1.5	7.8	-	105
0152023	KN 15 L-SIL-S	NiCr/Ni	DIN KCA	SIL-SIL-S round	2 x 1.5	7.8	-	105
0162023	KN 15 L-SIL-S	NiCr/Ni	IEC KCA	SIL-SIL-S round	2 x 1.5	7.8	-	105
0153023	KP 15 L-SIL-S	PtRh/Pt	DIN RCB, SCB	SIL-SIL-S round	2 x 1.5	7.8	-	105
0163023	KP 15 L-SIL-S	PtRh/Pt	IEC RCB, SCB	SIL-SIL-S round	2 x 1.5	7.8	-	105
0151007	KE 4 L-SIL-S	Fe/CuNi	DIN LX	SIL-SIL-S ovale	2 x 1.5	-	8 x 5.2	85
0161007	KE 4 L-SIL-S	Fe/CuNi	IEC JX	SIL-SIL-S ovale	2 x 1.5	-	8 x 5.2	85
0152007	KN 4 L-SIL-S	NiCr/Ni	DIN KCA	SIL-SIL-S ovale	2 x 1.5	-	8 x 5.2	85
0162007	KN 4 L-SIL-S	NiCr/Ni	IEC KCA	SIL-SIL-S ovale	2 x 1.5	-	8 x 5.2	85
0153007	KP 4 L-SIL-S	PtRh/Pt	DIN RCB, SCB	SIL-SIL-S ovale	2 x 1.5	-	8 x 5.2	85
0163007	KP 4 L-SIL-S	PtRh/Pt	IEC RCB, SCB	SIL-SIL-S ovale	2 x 1.5	-	8 x 5.2	85
0151019	KE 13 L-SIL	Fe/CuNi	DIN LX	SIL-GL ovale	2 x 1.5	-	6 x 3.3	50
0161019	KE 13 L-SIL	Fe/CuNi	IEC JX	SIL-GL ovale	2 x 1.5	-	6 x 3.3	50
0152019	KN 13 L-SIL	NiCr/Ni	DIN KCA	SIL-GL ovale	2 x 1.5	-	6 x 3.3	50
0162019	KN 13 L-SIL	NiCr/Ni	IEC KCA	SIL-GL ovale	2 x 1.5	-	6 x 3.3	50
0153019	KP 13 L-SIL	PtRh/Pt	DIN RCB, SCB	SIL-GL ovale	2 x 1.5	-	6 x 3.3	50
0151015	KE 11 L-SIL-S	Fe/CuNi	DIN LX	SIL-GL-S	2 x 1.5	6.7	-	82
0161015	KE 11 L-SIL-S	Fe/CuNi	IEC JX	SIL-GL-S	2 x 1.5	6.7	-	82
0152015	KN 11 L-SIL-S	NiCr/Ni	DIN KCA	SIL-GL-S	2 x 1.5	6.7	-	82

Last Update (01.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

Extension- and compensating cables, paired

Article number	Reference/article designation	Thermocouple	Product Make-up	Cable design	Number of cores and mm ² per conductor	Outer diameter [mm]	Outer dimensions, width x height (mm)	Weight (kg/km)
0162015	KN 11 L-SIL-S	NiCr/Ni	IEC KCA	SIL-GL-S	2 x 1.5	6.7	-	82
0153015	KP 11 L-SIL-S	PtRh/Pt	DIN RCB, SCB	SIL-GL-S	2 x 1.5	6.7	-	82
0163015	KP 11 L-SIL-S	PtRh/Pt	IEC RCB, SCB	SIL-GL-S	2 x 1.5	6.7	-	82
1161012	KP 11 L-SIL-S	NiCr/Ni	IEC KCA	SIL-GL-S ovale	2 x 1.5	-	6.8 x 4.1	82
Glass fibre-insulated versions 1.5 mm ²								
0151005	KE 3 L	Fe/CuNi	DIN LX	GL-GL ovale	2 x 1.5	-	5.1 x 2.7	64
0161005	KE 3 L	Fe/CuNi	IEC JX	GL-GL ovale	2 x 1.5	-	5.1 x 2.7	64
0152005	KN 3 L	NiCr/Ni	DIN KCA	GL-GL ovale	2 x 1.5	-	5.1 x 2.7	64
0162005	KN 3 L	NiCr/Ni	IEC KCA	GL-GL ovale	2 x 1.5	-	5.1 x 2.7	64
0153005	KP 3 L	PtRh/Pt	DIN RCB, SCB	GL-GL ovale	2 x 1.5	-	5.1 x 2.7	64
0163005	KP 3 L	PtRh/Pt	IEC RCB, SCB	GL-GL ovale	2 x 1.5	-	5.1 x 2.7	64
0151006	KE 4 L-S	Fe/CuNi	DIN LX	GL-GL-S ovale	2 x 1.5	-	5.9 x 3.7	87
0161006	KE 4 L-S	Fe/CuNi	IEC JX	GL-GL-S ovale	2 x 1.5	-	5.9 x 3.7	87
0152006	KN 4 L-S	NiCr/Ni	DIN KCA	GL-GL-S ovale	2 x 1.5	-	5.9 x 3.7	87
0162006	KN 4 L-S	NiCr/Ni	IEC KCA	GL-GL-S ovale	2 x 1.5	-	5.9 x 3.7	87
0153006	KP 4 L-S	PtRh/Pt	DIN RCB, SCB	GL-GL-S ovale	2 x 1.5	-	5.9 x 3.7	87
0163006	KP 4 L-S	PtRh/Pt	IEC RCB, SCB	GL-GL-S ovale	2 x 1.5	-	5.9 x 3.7	87

Last Update (01.09.2020)


©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Extension- and compensating cables, paired



Extension- and compensating cables, paired

