

## SILVYN® LTP 90° M

SILVYN® LTPW-M is a nickel-plated brass conduit fitting that offers a protection degree up to IP66/67/68/69



Corrosion-resistant



Maximum vibration protection



Mechanical resistance



Oil-resistant



Optimum strain relief



Robust

### Benefits

High tensile strength  
Vibration protection  
High sealing performance

### Application range

In combination with protective conduit:  
SILVYN® LTP  
Applications with high mechanical stress  
Used in areas where liquids are present

### Product Make-up

Metric connection thread  
90° hexagonal collar

Last Update (13.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® LTP 90° M

Threaded sleeve  
Cap nut

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001180 ETIM 5.0 Class-Description: Screw connection for protective metallic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001180 ETIM 6.0 Class-Description: Screw connection for protective metallic hose
Certifications:	IEC EN 61386-23
Material:	Body: nickel-plated brass Seal: PA compression seal
Protection rating:	IP66 IP67 IP68 (5 bar) IP69
Temperature range:	-50°C to +135°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® LTP 90° M**

Article number	Metric size	SW wrench size mm	Thread length mm	Suitable for SILVYN® LTP	Pieces / PU
SILVYN® LTP 90° M					
55510400	16 x 1.5/1	20.0	10	12	10
55510410	16 x 1.5/2	20.0	10	16	10
55510420	20 x 1.5/1	24.0	13	16	10
55510430	20 x 1.5/2	24.0	13	20	10
55510440	25 x 1.5	30.0	14	25	10
55510450	32 x 1.5	36.0	15	32	2
55510460	40 x 1.5	46.0	18	40	1
55510470	50 x 1.5	57.0	18	50	1
55510480	63 x 1.5	72.0	20	63	1

Last Update (13.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16