

SILVYN® LTP-E

SILVYN® LTP-E - nickel-plated brass insert

Info

Ensuring cables do not get damaged



Reliability



Temperature-resistant

Benefits

Cable damage can be prevented

Application range

Conduit end cover
If no conduit fitting is used

Product features

All-round collar completely covers the protective conduit end

Product Make-up

Threaded sleeve

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001180

ETIM 5.0 Class-Description: Screw connection for protective metallic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001180

ETIM 6.0 Class-Description: Screw connection for protective metallic hose

Last Update (15.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® LTP-E

Material: Nickel-plated brass
Temperature range: -50°C to +135°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® LTP-E

Article number	Nominal size	Suitable conduit nominal size	Pieces / PU
SILVYN® LTP-E			
61802300	10	1/4"	10
61802301	12	5/16"	10
61802302	16	3/8"	10
61802303	20	1/2"	10
61802305	25	3/4"	10
61802306	32	1"	10
61802307	40	1 1/4"	10
61802304	50	1 1/2"	4
61802308	63	2"	1

Last Update (15.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16