

ÖLFLEX® CLASSIC 100 450/750 V


Colour-coded PVC power and control cable

ÖLFLEX® CLASSIC 100 - flexible PVC cable, colour coded, power and control cable for various applications, 450/750V, also for YSLY or YY

Info

CPR: Article number choice under www.lappkabel.com/cpr

For nominal voltage U₀/U: 300/500V and conductor cross-sections below 2,5mm² see ÖLFLEX® CLASSIC 100 300/500V



Good chemical resistance



Torsion-resistant

Benefits

High electrical performance due to 4 kV test voltage

High flexibility due to short-twisted conductor layers

Application range

Plant engineering

Industrial machinery

Heating and air-conditioning systems

Power stations

Dry or damp rooms that are subject to medium mechanical loads

For fixed installation as well as occasional flexing at free, non-continuously recurring movement without tensile load

Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)

Product features

Flame-retardant according IEC 60332-1-2

Good chemical resistance, see catalogue appendix T1

Last Update (02.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® CLASSIC 100 450/750 V

Norm references / Approvals

Based on IEC 60227-5 and EN 50525-2-51

Based on EN 50525-2-11 and EN 50525-2-31

Product Make-up

Fine-wire strand made of bare copper wires

PVC insulation LAPP P8/1

Cores twisted in layers

PVC outer sheath, grey (similar RAL 7001)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class-Description: Flexible cable
Core identification code:	Up to 5 cores: colour-coded according to VDE 0293-308, refer to Appendix T9 From 6 cores: ÖLFLEX® colour code, refer to Appendix T7
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Torsion movement in WTG:	TW-0 & TW-1, refer to Appendix T0
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 4 x outer diameter
Nominal voltage:	U0/U: 450/750 VAC In protected and fixed installations: U0/U: 600/1000 V
Test voltage:	4000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -5 °C to +70 °C Fixed installation: -40 °C to +80 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Single lengths for sizes: ≥ 5G50 max. 500 m; ≥ 5G95 max. 400; ≥ 3G120 max. 500 m; ≥ 4G120 max. 300; ≥ 4G185 max. 250 m

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® CLASSIC 100 450/750 V**

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CLASSIC 100 450/750 V				
0010086	2 X 2.5	8.9	48	128
0010087	3 G 2.5	9.6	72	162
00100933	3 X 2.5	9.6	72	162
00100883	4 G 2.5	10.7	96	203
00100893	5 G 2.5	11.8	120	242
0010091	7 G 2.5	13.1	168	321
0010092	8 G 2.5	15.8	192	385
0010100	2 X 4.0	10.4	76.8	187
0010210	3 G 4.0	11.2	115.2	244
00101013	4 G 4.0	12.5	154	297
00101023	5 G 4.0	13.7	192	355
0010103	7 G 4.0	15.2	269	471
0010105	3 G 6.0	12.6	173	318
00101063	4 G 6.0	13.8	230	394
00101073	5 G 6.0	15.6	288	489
0010108	7 G 6.0	17.3	403	651
0010301	3 G 10.0	15.9	288	516
00101093	4 G 10.0	17.6	384	650
00101103	5 G 10.0	19.7	480	792
0010111	7 G 10.0	21.7	672	1058
0010302	3 G 16.0	18.3	461	728
00101123	4 G 16.0	20.4	614	1087
00101133	5 G 16.0	22.8	768	1118
0010303	3 G 25.0	23	720	1388
00101153	4 G 25.0	25.4	960	1582
00101163	5 G 25.0	28.5	1200	1771
0010304	3 G 35.0	25.6	1008	1766
00101173	4 G 35.0	28.5	1344	2106
00101183	5 G 35.0	31.9	1680	2635
0010305	3 G 50.0	31	1440	2556
00101193	4 G 50.0	34.5	1920	2943
00103133	5 G 50.0	38.6	2400	3936
0010306	3 G 70.0	35.3	2016	3182

Last Update (02.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16



ÖLFLEX® CLASSIC 100 450/750 V

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
00101203	4 G 70.0	39.4	2688	4092
00103143	5 G 70.0	44.1	3360	4800
0010307	3 G 95.0	41.3	2736	4675
00101213	4 G 95.0	45.8	3648	5290
00103153	5 G 95.0	51.6	4560	5600
0010308	3 G 120.0	47.6	3456	5626
00103093	4 G 120.0	53.1	4608	6994
00103113	4 G 150.0	57.4	5760	7500
00103123	4 G 185.0	62.8	7104	8300

Last Update (02.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16