

## SILVYN® KSE-M

SILVYN® KSE-M - metric conduit fitting with integrated EMC screening for SILVYN® FPAS



Maximum vibration protection



Optimum strain relief



Reliability



Integrated SKINTOP<sup>®</sup> cable gland



Interference signals



UV-resistant

### Benefits

Fast assembly  
Vibration protection  
Additional cable strain relief  
Additional cable sealing  
Optimum screen connection (EMC)

### Application range

In combination with protective conduit:  
SILVYN® FPAS  
Used in areas where screened cables and wires need to have additional protection

### Product features

In black colour UV-resistant and weather-proofed

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SILVYN® KSE-M

Removeable with a screwdriver

### Norm references / Approvals

UL FILENUMBER E308201

### Product Make-up

Metric connection thread

EMC cable gland

Upper part with integrated all-round toothing

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Certifications:

IEC EN 61386-23

On request:

without EMC contacts

Colour delivered:

Black (RAL 9005), UV-resistant

Material:

Nickel-plated brass

PA66

Halogen-free

Protection rating:

Conduit: IP66

Cable: IP68

Temperature range:

-30 °C to +100 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® KSE-M**

Article number	Metric size	Clamping range in mm	Thread length mm	Suitable for SILVYN® FPAS	For conduit with outer Ø (mm)	Pieces / PU
SILVYN® KSE-M black						
55507105	16 x 1.5/1	4.5 - 9	12	13	13,0	10
55507115	16 x 1.5/2	4.5 - 9	12	16	15,8	10
55507125	20 x 1.5/1	7 - 12.5	12	16	15,8	10
55507135	20 x 1.5/2	7 - 12.5	12	21	21,2	10
55507145	25x1.5	9 - 16.5	12	28	28,5	10
55507155	32 x 1.5	11 - 21	15	34	34,5	10
55507165	40x1.5	19 - 28	15	42	42,5	1
55507175	50 x 1.5	27 - 35	15	54	54,5	1

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16