

SILVYN® TC

SILVYN® TC is a parallel corrugated conduit with an innovative design due to integrated metric threads, mountable with standard metric counter nut

Info

No conduit gland required

With counter nut usable

Selected section length



Good chemical resistance



Halogen-free



Assembly time



Low weight



UV-resistant

Benefits

Dimensionally stable

Flexible

Threaded

Cost-saving due to quick and easy installation

Application range

Control cabinet manufacturing

Mechanical engineering

Plant engineering

For indoor and outdoor use

Product features

Halogen and cadmium-free

Abrasion-resistant

Last Update (26.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® TC

High resistance to oil, petrol, acids and other chemicals

Product Make-up

Fine-profile corrugated polyamide 6 conduit

Note

We recommend to use an additional sealing to maximize the IP rating
Section length 222 mm

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001175 ETIM 5.0 Class-Description: Corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001175 ETIM 6.0 Class-Description: Corrugated plastic hose
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	PA 6 Halogen-free Fire behaviour according to UL 94 V-2
Temperature range:	-40 °C to +120 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SILVYN® TC

Article number	Nominal size	ID x OD mm	Metric size	PU ring (m)
61221035	17	16.6 x 21.2	20 x 1.5	50
64400650	22	23.1 x 28.4	25 x 1.5	50
64400651	26	28.9 x 34.5	32 x 1.5	50
64400826	37	34 x 42.2	40 x 1.5	50

Last Update (26.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16