

ÖLFLEX® CLASSIC 110 LT

Cold flexible PVC control cable, suitable for low temperatures as well as outdoor use

ÖLFLEX® CLASSIC 110 LT - PVC control cable, cold-resistant, flexible, UV-resistant, for low temperature and outdoor use, 300/500V, also for YSLY or YY arctic grade

Info

CPR: Article number choice under www.lappkabel.com/cpr

UV and weather-resistant according to ISO 4892-2



Suitable for outdoor use



Cold-resistant



Torsion-resistant



UV-resistant

Benefits

Inexpensive control cable for flexing outdoor use

Space-saving installation due to small cable diameters

High electrical performance due to 4 kV test voltage

Application range

Plant engineering

Industrial machinery

Heating and air-conditioning systems

Freezing plants, cold storage

Suitable for outdoor applications

Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® CLASSIC 110 LT

Product features

Flame-retardant according IEC 60332-1-2
Flexible down to -30°C
UV and weather-resistant according to ISO 4892-2
Ozone-resistant according to EN 50396

Norm references / Approvals

Based on EN 50525-2-51

Product Make-up

Fine-wire strand made of bare copper wires
Core insulation: PVC, cold-resistant
Cores twisted in layers
Outer sheath: PVC, cold-resistant, black

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	Black with white numbers acc. to VDE 0293-334
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Torsion movement in WTG:	TW-0 & TW-2, refer to Appendix T0
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 4 x outer diameter
Nominal voltage:	U0/U: 300/500 V
Test voltage:	4000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -30°C to +70°C Fixed installation: -40°C to +80°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® CLASSIC 110 LT

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1120730	2 X 0.75	5.4	14.4	45
1120731	3 X 0.75	5.7	21.6	55
1120732	3 G 0.75	5.7	21.6	55
1120733	4 X 0.75	6.2	28.8	66
1120734	4 G 0.75	6.2	28.8	66
1120735	5 G 0.75	6.7	36	79
1120736	7 G 0.75	7.3	50.4	101
1120737	12 G 0.75	9.9	86.4	171
1120738	18 G 0.75	11.7	130	244
1120739	25 G 0.75	13.8	180	337
1120740	2 X 1.0	5.7	19.2	53
1120741	3 X 1.0	6	28.8	65
1120742	3 G 1.0	6	28.8	65
1120743	4 X 1.0	6.5	38.4	79
1120744	4 G 1.0	6.5	38.4	79
1120745	5 G 1.0	7.1	48	94
1120746	7 G 1.0	8	67.2	126
1120747	12 G 1.0	10.5	115	205
1120748	18 G 1.0	12.7	173	300
1120749	25 G 1.0	14.7	240	408
1120750	2 X 1.5	6.3	29	68
1120751	3 X 1.5	6.7	43	84
1120752	3 G 1.5	6.7	43	84
1120753	4 X 1.5	7.2	58	104
1120754	4 G 1.5	7.2	58	104
1120755	5 X 1.5	8.1	72	128
1120756	5 G 1.5	8.1	72	128
1120757	7 X 1.5	8.9	101	166
1120758	7 G 1.5	8.9	101	166
1120759	12 G 1.5	12	173	279
1120760	18 G 1.5	14.4	259	407
1120761	25 G 1.5	16.9	360	560
1120762	2 X 2.5	7.5	48	101
1120763	3 G 2.5	8.1	72	132

Last Update (11.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

ÖLFLEX® CLASSIC 110 LT

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1120764	4 G 2.5	8.9	96	163
1120765	5 G 2.5	10	120	200
1120766	7 G 2.5	11.1	168	267
1120767	12 G 2.5	14.8	288	445
1120768	18 G 2.5	17.8	432	648
1120769	25 G 2.5	20.8	600	890
1120770	4 G 4.0	10.8	154	249
1120771	5 G 4.0	12.1	192	305
1120772	4 G 6.0	13	230	365
1120773	5 G 6.0	14.5	288	447

Last Update (1.1.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16