

## SILVYN® AFW-PA

SILVYN® AFW-PA is a one-piece angled connection flange especially designed for SILVYN® MAXI PA



Assembly time



Robust



Reliability

### Benefits

Tear-resistant connection  
Secure conduit insertion

### Application range

In combination with protective conduit  
SILVYN® MAXI PA  
Mechanical engineering  
Bundling and guiding of cables and wires

### Product Make-up

One-piece 90° elbow connector with clap mechanism specifically designed for use with the SILVYN® MAXI PA. Thanks to the special design, the conduit can be pre-locked and mounted ready for connection

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001176

ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001176

ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose

Colour delivered:

Grey (RAL 7001)

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**SILVYN® AFW-PA**

Material:	Black (RAL 9005), UV-resistant PA6 Halogen-free
Protection rating:	IP 54 IP 65 with AFG-PA/AFW-PA seal
Temperature range:	-40 °C to +115 °C

**Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**SILVYN® AFW-PA**

Article number	Nominal size	Pieces / PU
SILVYN® AFW-PA 90° grey		
55001090	70	1
55001091	95	1
SILVYN® AFW-PA 90° black		
55001093	70	1
55001092	95	1