

## ÖLFLEX® CLASSIC 115 CY BK

Screened PVC control cable with small outer diameter and black outer sheath

ÖLFLEX® CLASSIC 115 CY BK - PVC control cable, screened and flexible for various applications, also outdoors. Thin and light without inner sheath, U<sub>0</sub>/U 300/500V

### Info

With black outer sheath, UV-resistant  
Thin and light, without inner sheath  
EMC-compliant



Good chemical resistance



Interference signals



Torsion-resistant



UV-resistant

### Benefits

Suitable for outdoor applications  
Space-saving installation due to small cable diameters

### Application range

Measurement and control technology  
Plant engineering  
Industrial machinery  
Heating and air-conditioning systems  
Conveyor and transport systems  
Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

# ÖLFLEX® CLASSIC 115 CY BK

Suitable for outdoor applications

## Product features

UV and weather-resistant according to ISO 4892-2  
Flame-retardant according IEC 60332-1-2  
Good chemical resistance, see catalogue appendix T1  
High degree of screening  
low transfer impedance  
(max. 250  $\Omega$ /km at 30 MHz)

## Norm references / Approvals

Based on EN 50525-2-51

## Product Make-up

Fine-wire strand made of bare copper wires  
PVC insulation LAPP P8/1  
Cores twisted in layers  
Plastic foil wrapping  
Tinned-copper braiding  
PVC outer sheath, black

## Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	Black with white numbers acc. to VDE 0293-334
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Torsion movement in WTG:	TW-0 & TW-1, refer to Appendix T0
Minimum bending radius:	Occasional flexing: 20 x outer diameter Fixed installation: 6 x outer diameter
Nominal voltage:	U0/U: 300/500 V
Test voltage:	Core/core: 4000 V Core/screen: 2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -5 °C to +70 °C Fixed installation: -40 °C to +80 °C

## Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil  $\leq$  30 kg or  $\leq$  250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## ÖLFLEX® CLASSIC 115 CY BK

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® CLASSIC 115 CY BK**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1136510	2 X 0.5	5.8	36	54
1136511	3 G 0.5	6.1	43	63
1136512	3 X 0.5	6.1	43	63
1136513	4 G 0.5	6.5	49	71
1136514	4 X 0.5	6.5	49	71
1136515	5 G 0.5	7	57	86
1136516	5 X 0.5	7	57	86
1136517	7 G 0.5	7.5	69	105
1136518	7 X 0.5	7.5	69	105
1136519	12 G 0.5	9.9	104	163
1136520	12 X 0.5	9.9	104	163
1136521	18 G 0.5	11.5	141	226
1136522	25 G 0.5	13.4	211	350
1136523	2 X 0.75	6.2	43	59
1136110	3 G 0.75	6.5	52	76
1136525	3 X 0.75	6.5	52	76
1136111	4 G 0.75	7	61	91
1136527	4 X 0.75	7	61	91
1136113	5 G 0.75	7.7	72	100
1136529	5 X 0.75	7.7	72	100
1136114	7 G 0.75	8.3	89	127
1136531	7 X 0.75	8.3	89	127
1136115	12 G 0.75	10.9	138	232
1136533	18 G 0.75	12.7	211	292
1136534	25 G 0.75	14.8	280	435
1136535	2 X 1.0	6.5	51	71
1136536	3 G 1.0	6.8	62	86
1136537	3 X 1.0	6.8	62	86
1136538	4 G 1.0	7.3	74	98
1136539	4 X 1.0	7.3	74	98
1136540	5 G 1.0	8.1	88	121
1136541	5 X 1.0	8.1	88	121
1136542	7 G 1.0	8.8	112	147
1136543	7 X 1.0	8.8	112	147

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

**ÖLFLEX® CLASSIC 115 CY BK**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1136544	12 G 1.0	11.5	185	249
1136545	18 G 1.0	13.9	268	364
1136546	25 G 1.0	15.9	354	486
1136547	2 X 1.5	7.1	65	86
1136548	3 G 1.5	7.5	82	112
1136549	3 X 1.5	7.5	82	112
1136550	4 G 1.5	8.2	100	135
1136551	4 X 1.5	8.2	100	135
1136552	5 G 1.5	8.9	119	148
1136553	5 X 1.5	8.9	119	148
1136554	7 G 1.5	9.9	154	192
1136555	7 X 1.5	9.9	154	192
1136556	12 G 1.5	13	268	332
1136557	18 G 1.5	15.6	373	484
1136558	25 G 1.5	17.9	530	734
1136559	34 G 1.5	20.8	683	944
1136560	3 G 2.5	8.9	118	151
1136561	4 G 2.5	9.9	147	188
1136562	5 G 2.5	11	176	224
1136563	7 G 2.5	11.9	253	294
1136564	12 G 2.5	16	355	521
1136565	18 G 2.5	19	569	740
1136566	4 G 4.0	11.6	248	287
1136567	4 G 6.0	14.2	343	424
1136568	4 G 10.0	17.2	495	637
1136569	5 G 10.0	19.5	592	824
1136570	4 G 16.0	20.2	800	1050
1136571	5 G 16.0	22.6	895	1285
1136572	4 G 25.0	25.1	1075	1413
1136573	4 G 35.0	28	1576	1867

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16